



JavaScript seems to be disabled in your browser.

You must have JavaScript enabled in your browser to utilize the functionality of this website.

Wiha Tools Canada  selling **Wiha** made hand tools in Canada since 2007



IBEW-NECA
DISCOUNT

 1-866-494-0096  Cart ▾

[Account](#) | [Log In](#) | [Contact Us](#) | [Distributors](#)

 [Wiha Tools No Hassle Guarantee](#)

 **Menu**

- [Torx](#) +
- [Torque Tools](#) +
- [Tech Tools](#) +
- [Shop Tools](#) +
- [Screwdrivers](#) +
- [Pliers](#) +
- [Insulated Tools](#) +
- [Hex](#) +
- [ESD Safe](#) +
- [Bits & Sets](#) +
- [Best Sellers](#)

[Home](#) → [Pliers](#) → [Precision Electronic Pliers](#) → [Electronic Oblique 48° Cutters Full Flush](#)

Electronic Oblique 48° Cutters Full Flush





Zoom

Titles and descriptions supersede the photo. We typically use the same image for different sizes of tools.

Precision Electronic Oblique 48° Cutters Full Flush

SKU: 56833

Add to Cart

Qty:

1



Share on Facebook



Tweet This



Pin it

Frequently bought together



Add selected to cart

- This item: [Electronic Oblique 48° Cutters Full Flush](#)
- [General Purpose Zipper Bag](#)
- [Utility Organizer Zipper Pouch](#)

Details

Ergonomic Molded Two Component Soft Comfort Grips
 Molded in Slip guards for added user protection
 Finger jam protection for safe operation at all settings
 Black Anti-Glare Finish
 Precise Cutting Edges in 48° angle
 Soft Touch Tension Return Springs


Additional Info

Packaging	Clamshell
SKU	56833
Weight (lbs)	0.2200
PROP 65	yes
Pliers Grip Type	Electronic
Precision Pliers Type	Oblique
Pliers OAL	5.5
Flush Cut Type	Ultra Full Flush


Pliers Nose Angle	48
Jaw Length	.393" (10.0mm)
Jaw Thickness	.1968" (5.0mm)
Jaw Width	.53" (13.5mm)
UPC	084705568331
UNSPSC	27112148

You may also be interested in the following product(s)


<
>




Electronic Pointed Short Nose Pliers



Electronic Diagonal Cutters Full Flush Narrow Shape




Electronic Diagonal Cutters Full Flush With Wire Trapping Spring




Electronic Diagonal Cutters Semi Flush Wide Pointed Head

Customers Also Bought


<
>




Precision Slotted/Phillips Screwdrivers 7 Piece Set



MagicRing® Screw Holding Ball Hex Inch and Metric L-Key Set in ErgoStar holder



Industrial Pliers SoftGrip 3 Piece



Precision Torx® Screwdriver 8 Piece Set T1-T8

Wiha Professional Quality Hand Tools

Wiha Tools Canada Ltd. Since 2007

Wiha Canadian operations started bringing

Wiha Tools Canada Ltd.

A wholly owned Subsidiary of Willi Hahn Corporation



We produce Wiha products around the world under strict ISO quality standards. State of the art technology and special tool steels

assure products consistent with our reputation for outstanding performance in demanding service, repair and production applications.

- [Download Catalogs](#)
- [Discounts and promotions](#)
- [Filter and sort all Wiha hand tools](#)

Wiha quality to professional tool users in 2007 with a warehouse located in Brampton, Ontario and sales office in the Greater Toronto Area.

- [About Us](#)
- [Privacy Policy](#)
- [Terms and Conditions](#)
- [Check the status of your order](#)
- [Having technical issues with the website?](#)

Monday - Friday office hours 8AM - 5PM CST USA

No products are stocked at this location

394 Deerhurst Drive
Brampton, ON, L6T 5H9
Customer Service Email: info@wihatools.ca
Tel: **1(866) 494-0096**
Fax: 1(800) 494-7456
GST/HST number Business Number: 82851 5551 RT0001

- [Shipping](#)
- [Returns](#)
- [Warranty Info](#)
- [About Us](#)
- [Privacy Policy](#)
- [Terms and Conditions](#)
- Over 5000 Professional Quality Wiha Tools In Stock**

