

Home -> Tool Types -> Pliers and Cutters -> ESD Safe Precision Short Round Nose Smooth Jaws Pliers

ESD Safe Precision Short Round Nose Smooth Jaws Pliers



Zoom

Be the first to review this product

ESD Safe Precision Short Round Nose Pliers, Smooth Jaws

SKU: 32750

Add to Cart

Qty: 1

Add to Wishlist Share on Facebook Tweet This Pin it

We accept

Details

Ergonomic Molded Two Component Soft Comfort Grips
Made of ESD-Safe Dissipative Material
Molded in Slip guards for added user protection
Finger jam protection for safe operation at all settings
High Quality Tool Steel, Mirror Polished Finish
Soft Touch Tension Return Springs

Additional Info

SKU	32750
Weight (lbs)	0.1700
Country of Manufacture	Germany

Grip Type	ESD Safe
Pliers Type	Round Nose
Precision Pliers Type	Round Nose
Overall Length	4 3/4"
Jaw Opening	1.13"
Jaw Length	1.02"
Jaw Thickness	.27"
Jaw Width	.38"

WRITE YOUR OWN REVIEW

Only registered users can write reviews. Please, [log in](#) or [register](#)

Warranty Info

Wiha Products Carry a **100% Satisfaction Guarantee**. All Wiha tools are guaranteed to be free of defects in workmanship and materials and will be replaced if found to be deficient providing tools have not been altered or misused. Wiha Insert Bits, Power Bits, Ceramic Tools and Tweezers are not warranted for use. Wiha Brand Torque control Tools are warranted for twelve months from date of purchase up to 5,000 torque Cycles.

[View Full Warranty](#)

You may also be interested in the following product(s)



ESD Safe Precision Small Tapered Head With Hollow Ground Back Semi Flush Cutters

Customers Also Bought



ESD Safe Precision Short Flat Nose Smooth Jaws Pliers

Wiha Professional Quality Hand Tools



We produce Wiha products around the world under strict ISO quality standards. State of the art technology and special tool steels

assure products consistent with our reputation for outstanding performance in demanding service, repair and production applications.

[Discounts and promotions](#)

[Military Discount](#)

[IBEW-NECA Discount](#)

[Filter and sort all Wiha hand tools](#)

[Complete list of tools](#)

Wiha Tools USA Since 1985

Wiha Activities In the USA Started in August of 1985 bringing Wiha quality to professional tool users in North America. Our USA warehouse and distribution center services all 50 states & Our New Facilities In Canada Supply millions of tools from stock to professional quality conscious tool users throughout North America.

[About Us](#)

[Privacy Policy](#)

[Terms and Conditions](#)

[Having technical issues with the website?](#)

We accept



Wiha Tools USA Willi Hahn Corporation

A Subsidiary of [Wiha Werkzeuge GmbH](#)
[Schonach Germany](#)

**Monday - Friday Office Hours 7am - 5pm
CST USA**

1348 Dundas Cir,
Monticello, MN 55362
Customer Service Email:
cservice@wihatools.com
Tel: 763-295-6591
Fax: 763-295-6598

[Shipping](#)

[Returns](#)

[Warranty Info](#)

[About Us](#)

[Privacy Policy](#)

[Terms and Conditions](#)

**Over 5000 Professional Quality Wiha Tools
In Stock**



Newsletter [Subscribe](#)

