

Home -> Best Sellers -> Precision Slotted/Phillips Screwdrivers 7 Piece Set

# Precision Slotted/Phillips Screwdrivers 7 Piece Set



Zoom

Be the first to review this product

Precision Slotted & Phillips Screwdriver 7 Piece Set Includes: Phillips #00, 0, 1 Slotted 1.5, 2.0, 2.5, 3.0mm

SKU: 26197

Add to Cart

Qty: 1

Add to Wishlist Share on Facebook Tweet This Pin it

We accept **amazon pay**

## Details

Wiha special chrome-vanadium-molybdenum tool steel  
Through hardened for best wear resistance  
Corrosion protective Vapor Chromed Finish  
Exact Fit Precision Machined Tips

## Additional Info

SKU	26197
Weight (lbs)	0.3100

Precision Handle is made of high Quality cadmium free Plastic  
 Molded on handle for permanent bond to blade  
 The Tapered Shape allows rapid rotation & precise control  
 Handles Proportioned to Blade Size for optimum torque  
 Precision free turning finger tip rotation cap.  
 Professional Quality Made In Germany

<b>Head Type</b>	slotted, phillips
<b>Country of Manufacture</b>	Germany
<b>Handle Grip Types</b>	Precision
<b>Phillips Sizes</b>	#00 #0 #1
<b>Slotted Sizes</b>	1.5mm~1/16" 2.0mm~5/64" 2.5mm ~3/32" 3.0mm~1/8"
<b>Pieces In Set</b>	7

## WRITE YOUR OWN REVIEW


Only registered users can write reviews. Please, [log in](#) or [register](#)

## Warranty Info

Wiha Products Carry a **100% Satisfaction Guarantee**. All Wiha tools are guaranteed to be free of defects in workmanship and materials and will be replaced if found to be deficient providing tools have not been altered or misused. Wiha Insert Bits, Power Bits, Ceramic Tools and Tweezers are not warranted for use. Wiha Brand Torque control Tools are warranted for twelve months from date of purchase up to 5,000 torque Cycles.


[View Full Warranty](#)

## You may also be interested in the following product(s)



Precision Slotted and Phillips  
 Screwdrivers - 8 Pc.Set Includes  
 Long Nose Pliers

## Customers Also Bought



Wiha Hat

## Wiha Professional Quality Hand Tools



We produce Wiha products around the world under strict ISO quality standards. State of the art technology and special tool steels

assure products consistent with our reputation for outstanding performance in demanding service, repair and production applications.

[Discounts and promotions](#)

[Military Discount](#)

[IBEW-NECA Discount](#)

[Filter and sort all Wiha hand tools](#)

[Complete list of tools](#)

## Wiha Tools in the USA Since 1985

Wiha Activities In the USA Started in August of 1985 bringing Wiha quality to professional tool users in North America. Our USA warehouse and distribution center services all 50 states & Our New Facilities In Canada Supply millions of tools from stock to professional quality conscious tool users through out North America.

[About Us](#)

[Privacy Policy](#)

[Terms and Conditions](#)

[Having technical issues with the website?](#)

We accept

The Amazon Pay logo, featuring the word 'amazon pay' in a stylized font with the Amazon smile arrow underneath.

## Wiha Quality Tools Willi Hahn Corporation

A Subsidiary of [Wiha Werkzeuge Gmbh](#)  
[Schonach Germany](#)

**Monday - Friday Office Hours 7am - 5pm  
CST USA**

1348 Dundas Cir,  
Monticello, MN 55362  
Customer Service Email:  
[cservice@wihatools.com](mailto:cservice@wihatools.com)  
Tel: 763-295-6591  
Fax: 763-295-6598

[Shipping](#)

[Returns](#)

[Warranty Info](#)

[About Us](#)

[Privacy Policy](#)

[Terms and Conditions](#)

**Over 5000 Professional Quality Wiha Tools  
In Stock**



**Newsletter** [Subscribe](#)