



JavaScript seems to be disabled in your browser.

You must have JavaScript enabled in your browser to utilize the functionality of this website.

Wiha Tools USA - selling **Wiha** made hand tools in the United States since 1985



+ SHIPS FREE
UPS FLAT RATE

**MILITARY
DISCOUNT
IBEW-NECA
DISCOUNT**

800-494-6104 Cart ▾

[Account](#) | [Quick Order](#) | [Log In](#) | [Contact Us](#) | [Checkout](#)

[Wiha Tools No Hassle Guarantee](#)

Menu

Torx +

Torque Tools +

Tech Tools +

Shop Tools +

Screwdrivers +

Pliers +

Insulated Tools +

Hex +

ESD Safe +

Bits & Sets +

Best Sellers

[Home](#) → [Tool Types](#) → [Screwdrivers](#) → [Insulated Slotted Screwdriver 2.5](#)

Insulated Slotted Screwdriver 2.5





Zoom

Titles and descriptions supersede the photo. We typically use the same image for different sizes of tools.

Insulated Cushion Grip Slotted Screwdriver 2.5 x 75mm (3/32")

SKU: 32010

Add to Cart

Qty: 1

- See additional sizes available
- Share on Facebook
- Tweet This
- Pin it

Frequently bought together



Add selected to cart

- This item: [Insulated Slotted Screwdriver 2.5](#)
- [General Purpose Zipper Bag](#)

Details

Insulated 1000 Volt Rated, 10,000 Volt Tested
 Meet ASTM , IEC, VDE, EN, ISO, NFPA
 All Tools Individually Tested for insulation Integrity, OSHA Compliant
 Ergo Molded Insulated Cushioned Grips, 1000 Volt Rated.
 Each Tool individually tested up to 10,000 Volts for insulation integrity.
 Handle & Insulation Molded On for maximum durability.
 Exact Fit Precision Machined Tips.
 Wiha Special CRM-72 Tool Steel Blades.
 Super Hardened and Tempered for long life performance.
 Guaranteed Quality, Made By Wiha.

Additional Info

SKU	32010
Weight (lbs)	0.0600
Packaging	Bag
California Residents	Click for Proposition 65 warning
Head Type	slotted
Handle Grip Types	Insulated SoftFinish®

Size Slotted	2.5mm
OAL MM	179
OAL Inch	7.1
Blade Length mm	75
Blade Length Inch	3
UPC	084705320106
UNSPSC	27111736

Customer Reviews



[Ask a Question](#)

[Write a Review](#)

Reviews **0** Questions **0**



Be the first to review this item

Customers Also Bought



Insulated Stripping Pliers 10-20 AWG

Wiha Professional Quality Hand Tools



Wiha Tools are covered by a No Hassle Guarantee

Wiha Tools USA Since 1985

Wiha Activities In the USA Started in August of 1985 bringing Wiha quality to professional tool users in North America. Our USA warehouse and distribution center services all 50 states & Our New Facilities In Canada Supply millions of tools from stock to professional quality conscious tool users throughout North America.

[About Us](#)
[Press](#)
[Authorized Distributor Login](#)
[Privacy Policy](#)

Wiha Tools USA Willi Hahn Corporation

A Subsidiary of [Wiha Werkzeuge GmbH](#) Schonach Germany

Monday - Friday office hours 8AM - 5PM CST USA

1348 Dundas Cir,
 Monticello, MN 55362
 Customer Service Email:
cservice@wihatools.com
 Tel: 763-295-6591

[Download Catalogs](#)
[Discounts and promotions](#)
[Military Discount](#)
[IBEW-NECA Discount](#)
[Wiha Manufacturing and Compliance](#)
[Wiha Tools USA Blog](#)
[Filter and sort all Wiha hand tools](#)
[Complete list of tools](#)

[Terms and Conditions](#)
[Check the status of your order](#)
[Having technical issues with the website?](#)



4.8 ★★★★★
Google
Customer Reviews

Fax: 763-295-6598
[Shipping](#)
[Returns](#)
[Warranty Info](#)
[Frequently Asked Questions](#)
[About Us](#)
[Privacy Policy](#)
[Terms and Conditions](#)
**Over 5000 Professional Quality Wiha Tools
In Stock**

