

Home → Tool Types → Torque Blades → Slotted Blades for TorqueFix or TorqueVario

Slotted Blades for TorqueFix or TorqueVario



Zoom

Titles and descriptions supersede the photo. We typically use the same image for different sizes of tools.

Be the first to review this product

Filter:

SKU	Product	Size Slotted	Max Torque In/lbs.	Max Torque Nm	Price	Qty
28534	Slotted Torque Blade 1.5mm		1.3 in/lbs.	0.15Nm		0
28535	Slotted Torque Blade 2.0mm		3.5 in/lbs.	0.4Nm		0
28536	Slotted Torque Blade 2.5mm		3.5 in/lbs.	0.4Nm		0
28537	Slotted Torque Blade 3.0mm		5.31 in/lbs.	0.6Nm		0
28538	Slotted Torque Blade 3.5mm		9.7 in/lbs.	1.1Nm		0
28539	Slotted Torque Blade 4.0mm		22.1 in/lbs.	2.5Nm		0

Add to Cart

We accept

amazon pay

Details

Wiha special chrome-vanadium-molybdenum tool steel
Through hardened for best wear resistance
Corrosion protective Hard Chrome Finish
Wiha ChromTop Finish on tip for a perfect fit every time
Color Coded: grey

Additional Info

Head Type	⊖ ⊖ slotted
Country of Manufacture	Germany
Torque Blades Compatible With	Easy Torque, iTorque, TorqueFix Wing Handle, TorqueVario
OAL MM	175mm

WRITE YOUR OWN REVIEW

Only registered users can write reviews. Please, [log in](#) or [register](#)

Warranty Info

Wiha Products Carry a **100% Satisfaction Guarantee**. All Wiha tools are guaranteed to be free of defects in workmanship and materials and will be replaced if found to be deficient providing tools have not been altered or misused. Wiha Insert Bits, Power Bits, Ceramic Tools and Tweezers are not warranted for use. Wiha Brand Torque control Tools are warranted for twelve months from date of purchase up to 5,000 torque Cycles.

[View Full Warranty](#)

You may also be interested in the following product(s)



TorqueVario Adjustable Inch
Pounds Handles

Wiha Professional Quality Hand Tools



We produce Wiha products around the world under strict ISO quality standards. State of the art technology and special tool steels

assure products consistent with our reputation for outstanding performance in demanding service, repair and production applications.

Wiha Tools USA Since 1985

Wiha Activities In the USA Started in August of 1985 bringing Wiha quality to professional tool users in North America. Our USA warehouse and distribution center services all 50 states & Our New Facilities In Canada Supply millions of tools from stock to professional quality conscious tool users throughout North America.

[About Us](#)
[Privacy Policy](#)
[Terms and Conditions](#)

Wiha Tools USA Willi Hahn Corporation

A Subsidiary of [Wiha Werkzeuge GmbH](#)
[Schonach Germany](#)

**Monday - Friday Office Hours 7am - 5pm
CST USA**

1348 Dundas Cir,
Monticello, MN 55362
Customer Service Email:
cservice@wihatools.com
Tel: 763-295-6591

[Discounts and promotions](#)

[Military Discount](#)

[IBEW-NECA Discount](#)

[Filter and sort all Wiha hand tools](#)

[Complete list of tools](#)

[Having technical issues with the website?](#)

We accept



Fax: 763-295-6598

[Shipping](#)

[Returns](#)

[Warranty Info](#)

[About Us](#)

[Privacy Policy](#)

[Terms and Conditions](#)

**Over 5000 Professional Quality Wiha Tools
In Stock**



Newsletter

Subscribe

