


Home → Tool Types → Screwdrivers → Insulated Slotted PicoFinish Screwdrivers

Insulated Slotted PicoFinish Screwdrivers



Zoom

Titles and descriptions supersede the photo. We typically use the same image for different sizes of tools.

Be the first to review this product

Filter:

SKU	Product	Size Slotted	OAL MM	Blade Length Inch	Price	Qty
32000	Insulated PicoFinish Slotted 1.5	1.5mm	154			0
32001	Insulated PicoFinish Slotted 2.0	2.0mm	154			0
32002	Insulated PicoFinish Slotted 2.5	2.5mm	160			0
32003	Insulated PicoFinish Slotted 3.0	3.0mm	160			0
32004	Insulated PicoFinish Slotted 3.5	3.5mm	160			0

Add to Cart

We accept

amazon pay

Details

Meets ASTM ,EN/ IEC, VDE, ISO, NFPA, CSA, OSHA Insulation Specifications
Precision Insulated Drivers 1000 Volt Rated
Insulation Molded On for maximum durability Wiha special chrome-vanadium-molybdenum tool steel
Through hardened for best wear resistance
Corrosion protective Hard Chrome Finish
Wiha ChromTop Finish on tip for a perfect fit every time
High Quality Components
Ergonomic Handle Design with Soft Zone for Comfortable Working
Investigated Handle Concept - Different Blade Sizes causes different Handle-Diameter Handle-Length is unchanging
Easy Movement Rotating Cap for Rapid Hand Action
Symbols on rotating Cap for easy Recognition of Size and Style

Additional Info

Head Type	☉☉ slotted
Country of Manufacture	Germany
Handle Grip Types	Insulated, PicoFinish

WRITE YOUR OWN REVIEW

Only registered users can write reviews. Please, [log in](#) or [register](#)

Warranty Info

Wiha Products Carry a **100% Satisfaction Guarantee**. All Wiha tools are guaranteed to be free of defects in workmanship and materials and will be replaced if found to be deficient providing tools have not been altered or misused. Wiha Insert Bits, Power Bits, Ceramic Tools and Tweezers are not warranted for use. Wiha Brand Torque control Tools are warranted for twelve months from date of purchase up to 5,000 torque Cycles.

[View Full Warranty](#)

You may also be interested in the following product(s)



Insulated Phillips PicoFinish
Screwdrivers

**Wiha Professional Quality
Hand Tools**

Wiha Tools USA Since 1985

Wiha Activities In the USA Started in August of
1985 bringing Wiha quality to professional tool

**Wiha Tools USA
Willi Hahn Corporation**

A Subsidiary of [Wiha Werkzeuge GmbH](#)



We produce Wiha products around the world under strict ISO quality standards. State of the art technology and special tool steels

assure products consistent with our reputation for outstanding performance in demanding service, repair and production applications.

[Discounts and promotions](#)

[Military Discount](#)

[IBEW-NECA Discount](#)

[Filter and sort all Wiha hand tools](#)

[Complete list of tools](#)

users in North America. Our USA warehouse and distribution center services all 50 states & Our New Facilities In Canada Supply millions of tools from stock to professional quality conscious tool users throughout North America.

[About Us](#)

[Privacy Policy](#)

[Terms and Conditions](#)

[Having technical issues with the website?](#)

We accept



[Schonach Germany](#)

**Monday - Friday Office Hours 7am - 5pm
CST USA**

1348 Dundas Cir,
Monticello, MN 55362
Customer Service Email:
cservice@wihatools.com
Tel: 763-295-6591
Fax: 763-295-6598

[Shipping](#)

[Returns](#)

[Warranty Info](#)

[About Us](#)

[Privacy Policy](#)

[Terms and Conditions](#)

**Over 5000 Professional Quality Wiha Tools
In Stock**



Newsletter [Subscribe](#)

