

Home → Tool Types → Insert Bits → Phillips Terminator Impact Insert Bit 10 Pack

Phillips Terminator Impact Insert Bit 10 Pack



Zoom

Titles and descriptions supersede the photo. We typically use the same image for different sizes of tools.

Be the first to review this product

Filter:

SKU	Product	Size Phillips	Country of Manufacture	Pack Quantity	Price	Qty
76501	Impact Insert Bit Phillips #1 - 10 PK	#1	Vietnam	10 Bits		<input type="text" value="0"/>
76502	Impact Insert Bit Phillips #2 - 10 PK	#2	Vietnam	10 Bits		<input type="text" value="0"/>
76503	Impact Insert Bit Phillips #3 - 10 PK	#3	Vietnam	10 Bits		<input type="text" value="0"/>

Add to Cart

We accept

amazon pay

Frequently bought together



Price for all selected :

Add selected to cart

This item: [Phillips Terminator Impact Insert Bit 10 Pack](#)

[SlimFix Locking 1/4" Bit Holder For 1/4" Insert Bits Impact Rated](#)

Details

Wiha Terminator High Performance Impact Bits
Up to 30 Times Performance Over Standard Bits In Impact Applications
Unique Molded On Bi-Material Torsion Zone, #1 Impact Rated
Standard 1/4" Drive - No special Adapter required
Special chrome-vanadium-molybdenum tool steel
Through hardened and tempered for best wear resistance
German Designed Professional Quality Made By Wiha

Additional Info

Head Type	⊕ ⊕ phillips
Pack Quantity	10 Bits
Bit Drive Size	1/4" Hex
Bit Length	29mm~1.1"
ISO Standard Size	C6.3
Coating	Red Molded Torsion Zone
Machine Hardness	HRC 59-61
Material	Impact resistant modified chrome-vanadium-molybdenum, tool steel, hardened

WRITE YOUR OWN REVIEW

Only registered users can write reviews. Please, [log in](#) or [register](#)

You may also be interested in the following product(s)



Pozidriv Terminator Impact Insert
Bit 10 Pack

**Wiha Professional Quality
Hand Tools**

Wiha Tools USA Since 1985

Wiha Activities In the USA Started in August of
1985 bringing Wiha quality to professional tool

**Wiha Tools USA
Willi Hahn Corporation**

A Subsidiary of [Wiha Werkzeuge GmbH](#)



We produce Wiha products around the world under strict ISO quality standards. State of the art technology and special tool steels

assure products consistent with our reputation for outstanding performance in demanding service, repair and production applications.

[Discounts and promotions](#)

[Military Discount](#)

[IBEW-NECA Discount](#)

[Filter and sort all Wiha hand tools](#)

[Complete list of tools](#)

users in North America. Our USA warehouse and distribution center services all 50 states & Our New Facilities In Canada Supply millions of tools from stock to professional quality conscious tool users throughout North America.

[About Us](#)

[Privacy Policy](#)

[Terms and Conditions](#)

[Having technical issues with the website?](#)

We accept



[Schonach Germany](#)

**Monday - Friday Office Hours 7am - 5pm
CST USA**

1348 Dundas Cir,
Monticello, MN 55362
Customer Service Email:
cservice@wihatools.com
Tel: 763-295-6591
Fax: 763-295-6598

[Shipping](#)

[Returns](#)

[Warranty Info](#)

[About Us](#)

[Privacy Policy](#)

[Terms and Conditions](#)

**Over 5000 Professional Quality Wiha Tools
In Stock**



Newsletter [Subscribe](#)

