


**COOPER**  
CooperTools  
**Xcelite®**



### TORX SCREWDRIVERS

The Torx driver system is now established in the automotive, consumer and other manufacturing industries. And now we bring it to you for repair work, hobby projects and do-it yourself activities.

Cat. No.	Point Size	Blade Dia.	Blade Length	Overall Length	Net Price
<b>XTD10</b>	T10	3/16"	3"	6 5/8"	<b>\$6.47</b>
<b>XTD15</b>	T15	3/16"	3"	6 5/8"	<b>6.47</b>
<b>XTD20</b>	T20	3/16"	3"	6 5/8"	<b>6.47</b>
<b>XTD25</b>	T25	3/16"	3"	6 5/8"	<b>6.47</b>
<b>XTD27</b>	T27	1/4"	4 1/2"	8 5/8"	<b>7.19</b>
<b>XTD30</b>	T30	1/4"	4 1/2"	8 5/8"	<b>7.19</b>



### PHILLIPS SCREWDRIVERS

Chrome vanadium steel blades. Precision points. Shockproof, breakproof, amber plastic handles.

Cat. No.	Point Size	Blade Dia.	Blade Length	Handle Dims.	Overall Length	Net Price
<b>POCKET CLIP STYLE</b>						
<b>P12SV</b>	0	1/8"	2"	1/2" x 2 1/4"	4 1/4"	<b>\$3.84</b>
<b>STUBBY</b>						
<b>SX101</b>	1	3/16"	1 7/16"	1 3/8" x 2"	3 3/8"	<b>6.36</b>
<b>SX102</b>	2	1/4"	1 5/16"	1 3/8" x 2"	3 3/8"	<b>7.14</b>
<b>REGULAR</b>						
<b>X100</b>	0	1/8"	2"	7/8" x 2 5/8"	4 5/8"	<b>4.28</b>
<b>X101V</b>	1	3/16"	3"	1" x 3 3/8"	6 5/8"	<b>5.70</b>
<b>X108V</b>	1	3/16"	6"	1" x 3 3/8"	9 5/8"	<b>7.52</b>
<b>X102V</b>	2	1/4"	4"	1 1/8" x 4 1/8"	8 1/8"	<b>7.62</b>
<b>X103</b>	3	5/16"	6"	1 1/4" x 4 1/2"	10 1/2"	<b>10.65</b>
<b>EXTRA LONG</b>						
<b>X1010</b>	1	3/16"	10"	1" x 3 3/8"	13 3/8"	<b>9.71</b>
<b>X1020</b>	2	1/4"	10"	1 1/8" x 4 1/8"	14 1/8"	<b>10.97</b>



### SCREWDRIVERS FOR SLOTTED SCREWS

Tough, AISI 6150 chrome vanadium steel blades are properly ground at the tip for greatest strength and best fit in screw slot. Securely embedded in handle, they won't turn or loosen. Shockproof, breakproof, amber plastic handles are shaped for perfect grip and balance.

Cat. No.	Blade Size	Blade Length	Handle Dims.	Overall Length	Net Price
<b>POCKET CLIP STYLE ROUND BLADE</b>					
<b>R3322V</b>	3/32"	2"	1/2" x 2 1/4"	4 1/4"	<b>\$2.94</b>
<b>R3323V</b>	3/32"	3"	1/2" x 2 1/4"	5 1/4"	<b>3.30</b>
<b>R3324V</b>	3/32"	4"	1/2" x 2 1/4"	6 1/4"	<b>3.51</b>
<b>R181V</b>	1/8"	2"	1/2" x 2 1/4"	4 1/4"	<b>2.87</b>
<b>R183V</b>	1/8"	3"	1/2" x 2 1/4"	5 1/4"	<b>3.51</b>
<b>STUBBY SQUARE BLADE</b>					
<b>S3161*</b>	3/16"	1 1/4"	1 3/16" x 2"	2 3/4"	<b>4.74</b>
<b>S141*</b>	1/4"	1 1/4"	1 3/16" x 2"	3 1/4"	<b>6.47</b>
<b>S5161*</b>	5/16"	1 1/4"	1 3/16" x 2"	3 1/4"	<b>5.37</b>
<b>REGULAR ROUND OR SQUARE BLADE</b>					
<b>R182V</b>	1/8"	2"	7/8" x 2 5/8"	4 5/8"	<b>3.51</b>
<b>R184V</b>	1/8"	4"	7/8" x 2 5/8"	6 5/8"	<b>4.55</b>
<b>R186V</b>	1/8"	6"	7/8" x 2 5/8"	8 5/8"	<b>4.92</b>
<b>R188V</b>	1/8"	8"	7/8" x 2 5/8"	10 5/8"	<b>5.31</b>
<b>R1810</b>	1/8"	10"	7/8" x 2 5/8"	12 5/8"	<b>5.70</b>
<b>R5323V</b>	5/32"	3"	7/8" x 2 5/8"	5 5/8"	<b>4.28</b>
<b>R5324V</b>	5/32"	4"	7/8" x 2 5/8"	6 5/8"	<b>4.28</b>
<b>R5325V</b>	5/32"	5"	7/8" x 2 5/8"	7 5/8"	<b>4.70</b>
<b>R5328</b>	5/32"	8"	7/8" x 2 5/8"	10 5/8"	<b>5.84</b>
<b>R3163</b>	3/16"	3"	1" x 3 3/8"	6 5/8"	<b>5.60</b>
<b>R3164V</b>	3/16"	4"	1" x 3 3/8"	7 5/8"	<b>6.60</b>
<b>R3166V</b>	3/16"	6"	1" x 3 3/8"	9 5/8"	<b>7.19</b>
<b>R3168V</b>	3/16"	8"	1" x 3 3/8"	11 5/8"	<b>7.74</b>
<b>R31610</b>	3/16"	10"	1" x 3 3/8"	13 5/8"	<b>8.91</b>
<b>R144V</b>	1/4"	4"	1 1/8" x 4 1/8"	8 1/8"	<b>7.58</b>
<b>R146V</b>	1/4"	6"	1 1/8" x 4 1/8"	10 1/8"	<b>8.48</b>
<b>R148V</b>	1/4"	8"	1 1/8" x 4 1/8"	12 1/8"	<b>9.24</b>
<b>R1410V</b>	1/4"	10"	1 1/8" x 4 1/8"	14 1/8"	<b>9.71</b>
<b>R5164</b>	5/16"	4"	1 1/4" x 4 1/2"	8 1/2"	<b>8.99</b>
<b>R5166</b>	5/16"	6"	1 1/4" x 4 1/2"	10 1/2"	<b>9.35</b>
<b>R5168</b>	5/16"	8"	1 1/4" x 4 1/2"	12 1/2"	<b>10.13</b>
<b>S51610*</b>	5/16"	10"	1 1/4" x 4 1/2"	14 1/2"	<b>13.40</b>
<b>R388</b>	3/8"	8"	1 3/8" x 4 1/2"	12 1/2"	<b>12.33</b>
<b>S3812*</b>	3/8"	12"	1 3/8" x 6"	18"	<b>17.09</b>

\*S—Square blade screwdrivers



### ROUND BLADE SCREWDRIVER SET

Contains 5 round blade screwdrivers for slotted screws. Nos. R182, R5324, R3166, R144 and R5166. Tools are instantly visible in the long-lasting plastic view case.

Cat. No.	Net Price
<b>SDR11</b>	<b>\$32.57</b>



### SCRULOX SCREWDRIVERS

ScruLox (Robertson type) square recess screws, developed in Canada and used extensively on appliances, radios, TV sets, electronic instruments, and many other products. They are often used for "tamper-proof" applications.

Cat. No.	Point Size	Handle Colour	Blade Length	Handle Dims.	Overall Length	Net Price
<b>SL1V</b>	1	Green	3 1/2"	1 1/8" x 4 1/8"	7 5/8"	<b>\$8.22</b>
<b>SL2V</b>	2	Red	3 1/2"	1 1/8" x 4 1/8"	7 5/8"	<b>8.22</b>