

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [130090-0009](#)  
**Status:** **Active**  
**Overview:** [Electric Reels](#)  
**Description:** Woodhead® Standard Duty Reel with Flying Leads, 16/3 SJTOW Cord, 10.67m (35.0') Cord Length

**Documents:**

[Drawing \(PDF\)](#) [Product Literature \(PDF\)](#)  
[RoHS Certificate of Compliance \(PDF\)](#)

**Agency Certification**

CSA LR29921  
 UL E22769

**General**

Product Family Electric Reels  
 Series [130090](#)  
 Cable Length 0.457m (1.50')  
 Comments Ratchet Lock (ON/OFF Switchable)  
 Depth 0.24m (9.59")  
 Duty Standard  
 Enclosure Rating NEMA 1  
 Height 0.32 (12.62")  
 NEMA Configuration NEMA 5-15  
 Overview [Electric Reels](#)  
 Product Literature Order No 987650-8061  
 Product Name Super-Safeway™  
 Type Cord Reel  
 UPC 78678875243  
 Width 13.06mm (5.160")  
 Woodhead Yes

**Physical**

Cable Movement Ratchet Lock  
 Cord Length 10.67m (35.0')  
 Drum Lock Ratchet  
 Material - Coating Powder Coating  
 Material - Housing Steel  
 Mounting Style Swinging  
 Net Weight 6.350/kg  
 Number of Conductors 3  
 Packaging Type Carton  
 Primary Cord/Cable Entry N/A  
 Retraction Weight 0.9kg (2.0 lb)  
 Wire Size AWG 16

**Electrical**

Bulb Included N/A  
 Cord Type 16/3 SJTOW  
 Current - Maximum per Contact 6A  
 GFCI No  
 Lamp Type N/A  
 Lamp Wattage - Maximum N/A  
 On/Off Switch N/A  
 Voltage - Maximum 120V

**Material Info**



**EU RoHS**

**Not RoHS Compliant**  
**REACH SVHC**  
 Not Reviewed  
**Low-Halogen Status**  
 Not Reviewed

**China RoHS**



**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

**Search Parts in this Series**

[130090Series](#)

Old Part Number

945-3

**Reference - Drawing Numbers**

Sales Drawing

SD-130090-001

This document was generated on 12/09/2014

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**