RCA TYPE (PHONO) CONNECTORS

PC MOUNT RCA JACK

Printed Circuit board mounting. A durable part, nylon body and nickel plated contacts. The mounting design affords considerable strain relief to protect PC board.

No. MS11 - single jack, package of five

No. MS13 - dual jack, Package of one

No. MS19 - triple jack, Package of one

* For bulk, add suffix letter "B" to Part No.

GOLD-PLATED. **TEFLON INSULATOR** RCA JACK



Panel mounting phono jack is gold plated and designed to be electrically superior as well as very durable; this is our best jack. Color bands for channel identification. Ground lug and nut also gold plated. Bushing measures 5/16" diameter with 9/32 across a flat.

No. MTG12 - display pack 1 red & 1 black

No. MTG12B-BL - bulk packed black No. MTG12B-RD - bulk packed red

GOLD PLATED ISOLATED RCA JACK



Panel mounting

phono jack is gold plated, mounts in a 3/8" dia. hole (shoulder washers included). Color bands for channel identification. Ground lug and nut are also Gold plated. Bushing measures 5/16".

No. 45-108G - display pack, 1 red & 1 black

No. 45-128G - display pack, 1 red & 1 white

No. 45-138G - display pack, 1 red, 1 white & 1 yellow

No. 45-148G - display pack, 2 vellow

No. 45-108GB BL - bulk packed. black

No. 45-108GB RD - bulk packed, red

No. 45-108GB WH - bulk packed, white

No. 45-108GB YE - bulk packed. vellow

PHONO JACKS Female RCA type

Solder terminals; body and shell molded plastic; integral strain relief. Available in red or black.



No. MS17 - display pkg, 1 red & 1 black No. MS17B RED - bulk packed, red

No. MS17B BLK - bulk packed, black

No. MS17B YEL - bulk packed, yellow

No. MS17B WHT - bulk packed, white

No. MS17B BLU - bulk packed, blue No. MS17B GRN - bulk packed, green

No. MS171 - display package,

1 red & 1 white for audio No. MS172 - display package,

1 each of red, white, yellow for A/V

No. MS173 - display package, 1 each of red, green, blue for component video

No. 70-022 - grey handle, display pkg. of 2

No. 70-022B - bulk packed

RCA or PHONO JACK

An industry standard and popular style jack that mounts in a 1/4" dia hole: up to 3/16" panel thickness. Mounting hardware is included.



No. MS12 - nickel plated, pack of five

No. MS12B RED - nickel plated.

bulk pack red No. MS12B BLK - nickel plated, bulk pack black

No. MS12B WHT - nickel plated, bulk pack white No. MS12B YEL - nickel plated, bulk pack Yellow

No. MSG12 - gold plated, pack of 2

No. MSG12B RD - gold plated,

bulk pack red No. MSG12B BL - gold plated,

bulk pack black No. 45-270B WH - gold plated.

bulk pack white

No. 45-270B YE - gold plated, bulk pack yellow

No. 45-270B BL - gold plated, bulk pack blue

No. 45-270B GR - gold plated, bulk pack green

No. 45-270B OR - gold plated, bulk pack orange

No. 45-270B BK - gold plated, bulk pack black

No. 45-270B RD - gold plated, bulk pack red

REAR MOUNT RCA JACK

Mounts in a 3/8" mounting hole into panels up to 3/16" thick.

No. MS22 - Display packaged of one No. MS22B - Bulk packed

CHASSIS MOUNT RCA JACKS

Traditionally used in audio applications, the RCA connector is often used for video and low voltage power as well. This series is made to be mounted in panel or chassis. Color

coded insulators for left or right channel, video etc.. Connector surfaces are nickel plated brass, solder lug surfaces are tinned. The insulator material is black plastic.

No. MS30 - single jack, white insulator

No. MS35 - dual jacks, red & white insulators

No. MS45 - triple jacks, red, white & yellow insulators

No. MS40 - four (quad) jacks, white, red, white, red insulators

Note: For mounting, dimensioned drawings are available via facsimile from Philmore.

* For bulk, add suffix letter "B" to Part No.

PHONO JACKS Female RCA type



Solder terminals; body and shell molded plastic; Available in red or black.

No. MS15 - display pkg, 1 red & 1 black No. MS15B-RED - bulk packed, red No. MS15B-BLK - bulk packed, black

RCA FEMALE ADAPTOR, or Coupler



Phono jacks on both ends, for mating cables with RCA

No. SAG13 - gold plated

No. SAG13B - gold plated, bulk packaged

No. 45-311G - shielded. Gold plated

No. SA13 - nickel plated

No. SA13B - nickel plated, bulk packaged

No. SAG23 - 2 RCA-2 RCA, gold plated

No. SAG23B - bulk packaged

No. 45-333G - 3 RCA-3 RCA, gold plated

No. 45-333GB - bulk packaged

RCA FEMALE. BULKHEAD



Isolated RCA to RCA feed thru jacks for audio & video. Mounts in a 3/8" (.375") Mtg. hole. Colored insulation.

No. 45-162G - Gold plated. Package of 3 (1 red, 1 white & 1 yellow)

No. 42-362 - Nickel plated. Package of 3 (1 red, 1 white & 1 yellow)