



G3 Blue Shower Maintenance Cleaner

Product# 1630

Product Description

G3 Blue Shower is non-flammable cleaner formulated to be powerful, yet economical. Eliminate brushing and scrubbing, saving time and materials. Clean oil and contaminants off of metal parts, printed circuit boards, barcode instruments, switch boxes, gear relays, and electronic motor controllers.

Techspray® has produced Blue Shower® maintenance cleaners for over 30 years, making Blue Shower a staple in maintenance departments all over the world!

Features / Benefits

- Powerful cleaner
- Non-flammable
- Rapid evaporation
- Zero residue
- Dielectric strength 27.3 kv
- Non-ozone depleting
- NSF registered K1 and K2

Applications

- Electrical Cleaning
- Plant Maintenance
- Transit Maintenance

Usage Instructions

Hold can 6-8 inches away. Direct spray to saturate soiled surface. A **TechBrush®** (2000 Series) may be utilized to help in the removal of heavy soils. When used as a general cleaner, start at top of area to be cleaned using a sweeping motion, and spray the area slowly, working towards the bottom. To clean in hard to reach areas, insert extension tube in sprayhead to direct spray. Allow components to dry completely before applying current. For flat surface cleaning, saturate a lint-free **TechClean®** Twillwipe (2357) or **Purwipe™** (2355) and wipe surface with cloth. Rotate the cleaning side of the wipe periodically and re-saturate.



Typical Product Data and physical Properties

Physical State:	Liquid, Aerosol
Color:	Clear, colorless
Odor:	Ethereal
Relative density:	1.229
Vapor Pressure:	122.7 kPa (920.45 mm Hg)
Evaporation rate:	>1 (butyl acetate = 1)
Heat of combustion:	0.84 kJ/g
Shelf life:	5 years

G3 Blue Shower Maintenance Cleaner Product# 1630

Material Compatibility

ABS:	Not Compatible
Nylon:	Excellent
Lexan:	Not Compatible
HDPE:	Excellent
LDPE:	Excellent
C.E.Phenolic	Excellent
PMMA:	Not Compatible
POM	Excellent
PP	Excellent
PS:	Not Compatible
PTFE:	Excellent
PVC:	Excellent

Packaging and Availability

1630-16S 16 oz.(454g) Aerosol Can

Environmental Policy

Techspray® is committed to developing products to ensure a safer and cleaner environment. We will continue to meet and sustain the regulations of all federal, state and local government agencies.

Resources

Techspray® products are supported by global sales, technical and customer services resources.

For additional technical information on this product or other Techspray® products in the United States, call the technical sales department at 800-858-4043, email tsales@techspray.com or visit our web site at: www.techspray.com.

Important Notice to Purchaser/User: The information in this publication is based on tests that we believe are reliable. The results may vary due to differences in tests type and conditions. We recommend that each user evaluate the product to determine its suitability for the intended application. Conditions of use are outside our control and vary widely. Techspray's only obligation and your only solution is replacement of product that is shown to be defective when you receive it. In no case will Techspray® be liable for any special, incidental, or consequential damages based on breach of warranty, negligence or any other theory.