






Pushbuttons/Selectors/Pilot Lights/Buzzers

AH165-2

Accessories

Description	Type																					
<p>Push-lock, turn-reset button</p>  <p>AF87-634</p>	<p>For illuminated pushbuttons (Used with 2VL, 2YVL)</p> <table border="0"> <tr> <td>Color</td> <td>Type</td> </tr> <tr> <td>Green</td> <td>AHX2616-G</td> </tr> <tr> <td>Red</td> <td>AHX2616-R</td> </tr> <tr> <td>White</td> <td>AHX2616-W</td> </tr> <tr> <td>Yellow</td> <td>AHX2616-Y</td> </tr> </table> <p>For pushbuttons (Used with 2V, 2YV)</p> <table border="0"> <tr> <td>Color</td> <td>Type</td> </tr> <tr> <td>Green</td> <td>AHX2615-G</td> </tr> <tr> <td>Red</td> <td>AHX2615-R</td> </tr> <tr> <td>Yellow</td> <td>AHX2615-Y</td> </tr> <tr> <td>Black</td> <td>AHX2615-B</td> </tr> </table>		Color	Type	Green	AHX2616-G	Red	AHX2616-R	White	AHX2616-W	Yellow	AHX2616-Y	Color	Type	Green	AHX2615-G	Red	AHX2615-R	Yellow	AHX2615-Y	Black	AHX2615-B
Color	Type																					
Green	AHX2616-G																					
Red	AHX2616-R																					
White	AHX2616-W																					
Yellow	AHX2616-Y																					
Color	Type																					
Green	AHX2615-G																					
Red	AHX2615-R																					
Yellow	AHX2615-Y																					
Black	AHX2615-B																					
<p>Dust-tight cover</p>  <p>AF87-636</p>	<p>For flush round (Used with 2F, 2FL, 2F5, 2FL5) Type: AHX2603-2</p> <p>For flush square (Used with 2SF, 2SFL, 2SF5, 2SFL5) Type: AHX2603-2S</p> <p>These covers protect against dust.</p>																					
<p>Key washer</p>  <p>AF87-635</p>	<p>Type: AHX2601</p> <p>Mounting hole, mm</p> 																					
<p>Key</p>  <p>AF94-464</p>	<p>Type</p>	<p>Used with</p> <table border="0"> <tr> <td>AHX662-□</td> <td>AH164-J, SJ, JK, SJK AH165-J, SJ, JK, SJK, JM, RJM</td> </tr> <tr> <td>AR9C022-□</td> <td>AH165-2J, 2YJ</td> </tr> </table> <p>Note: Replace the □ mark by the key type code.</p> <p>Code: A, B, C, D, E, F Types</p>	AHX662-□	AH164-J, SJ, JK, SJK AH165-J, SJ, JK, SJK, JM, RJM	AR9C022-□	AH165-2J, 2YJ																
AHX662-□	AH164-J, SJ, JK, SJK AH165-J, SJ, JK, SJK, JM, RJM																					
AR9C022-□	AH165-2J, 2YJ																					