

Search This Product Catalog

By Keyword

Component Handling Solutions

Product Catalog for Component Handling Solutions

- 3Mâ„¢ Permanent Flooring Systems
- 3Mâ„¢ Static Control Packaging and Transportation Products
- 3Mâ„¢ Static Control Workstation Solutions**
- 3Mâ„¢ Tapes
- 3Mâ„¢ Test Equipment
- Tape & Reel

Where to Buy

- 3M Contacts
- US Static Control Distributors
- Canada Static Control Distributors

Other Tools

- ESD Training
- FAQs
- Tradeshows
- Samples
- MSDS Search
- Regulatory Issues

Related Sites

- Interconnect Solutions
- Microinterconnect Solutions
- All Electronic Solutions

- [Product Catalog for Component Handling Solutions](#)
- [3Mâ„¢ Static Control Workstation Solutions](#)
- [3Mâ„¢ Table, Floor Mats and Runners](#)
- [3Mâ„¢ Dissipative Rubber Mats and Floor Runners](#)

## 3Mâ„¢ Dissipative Rubber Table Mat, 8811

[Printer-friendly format](#)



Dissipative table mats include two 3Mâ„¢ Snap Fasteners 3034 (installed) and one 3Mâ„¢ Wrist Strap Grounding System 3048.

[\[click to enlarge\]](#)

GTIN(UPC/EAN) : 0 00 51138 37645 1  
3M Id : 98 - 0798 - 2554 - 7

### Additional Information

3M Static Dissipative Rubber Mats and Rolls 8800 Series consist of a top layer of static dissipative rubber laminated to a bottom layer of conductive rubber. Both layers are made from vulcanized synthetic which offers excellent resistance to oil, grease and most common solvents. They offer superior resistance to heat and hot solder as compared to vinyl or olefinic materials. Non - standard

[Full Text . . .](#)

### Characteristics

<b>Color</b>	Blue
<b>Construction</b>	Dual-Layer
<b>EPC Can View</b>	Public
<b>Hardness</b>	60 Shore A
<b>Length</b>	4 Linear Foot
<b>Material</b>	Rubber
<b>Rubber Composition</b>	Static-dissipative
<b>Thickness</b>	0.065 Inch
<b>Width</b>	2 Linear Foot

### Learn More . . .

[3M Static Control Products Overview - Brochure \(PDF 381.5 K\)](#)

[3Mâ„¢ Static Dissipative Rubber Mats & Runners 8800 Properties - Technical Information \(PDF 26.6 K\)](#)

**Please Note:**

Adobe® Acrobat® Reader is required to view PDF documents.

