




OGA DIAG 34.16 [867.67]
 VA DIAG 31.81 [807.87]
 PA DIAG 30.00 [762.00]



TOP LEVEL NUMBER	US NUMBER	CHINA NUMBER	TYPE	DM Y (TOTAL GLASS TO CONNECTION)	M/G FINISH	PROD SPEC
17-8951-205	98-0003-2678-9	59-0000-0080-8	FFC	8.00" [203.20]	AG500	23655
17-8951-227	98-0003-2681-3	59-0000-0174-9	SER	8.00" [203.20]	AG500	23655
17-8951-206	98-0003-2679-7	59-0000-0081-6	NOV	SEE DMG	AG500	23655
17-8951-226	98-0003-3029-4	59-0000-0082-4	USB R	8.00" [203.20]	AG500	23655



1.47±.020 [3.73±.51]
 TOTAL THICKNESS
 OF GLASS, CABLE
 AND STRAIN RELIEF

PINOUT	1	2	3	4	5
UL	UL	UR	SHLD	LR	LL

- NOTES:
1. WEIGHT OF GLASS IN GRAMS: 2533 ±10%
 2. NICOMATIC HOUSING P/N: OLOS
 3. NICOMATIC RECEPTACLES (PINS) MATTE TIN PLATED P/N: 14106-12
 4. HOUSING ORIENTED WITH LATCH DOWN

UNITS	INCHES [MM]
1	UL
2	UR
3	SHLD
4	LR
5	LL

REV	DESCRIPTION	DATE	BY
J	REVISED PER CO 033533	11/11	SB
H	REVISED PER CO 033454	8/11	SB
G	REVISED PER CO 033064	6/11	SB

MARKETING DRAWING
 SCT32NN 31.81" W