


# MASTER<sup>®</sup> APPLIANCE

Designers and Manufacturers of Heat Tools for Industry

## Master Heat Gun<sup>®</sup>



**Over 50 years  
of Professional  
Quality Heat**



### ***Master HG Series Heat Guns***

- The original Industrial Quality Heat Gun introduced to the worldwide marketplace in 1958. Made in the USA and used by legions of professional craftsmen for hundreds of applications that require fast, reliable, flameless heat.
- Powerful universal motor delivers strong 23 CFM airflow at temperatures up to 1000°F/540°C to get the job done fast. Double protected heating element and sturdy die-cast aluminum housing provide years of reliable service.
- Easily replaceable heating element and motor brushes allow for fast field maintenance, to keep your Master Heat Gun working year after year in factories, laboratories, workshops and jobsites.
- A broad range of optional attachments make Master Heat Guns ideal for a wide variety of heating, shrinking, drying, welding and soldering applications.

# MASTER HEAT GUN®

## Heavy-Duty Industrial Quality Multiple Use Heat Gun

Wherever reliable flameless heat is required, the MASTER HEAT GUN® does the job faster, safer and better.

High temperature industrial jobs are done faster with the MASTER HEAT GUN because of its higher power and airflow ratings.

Power ratings go up to 1000°F/540°C at 1740 watts (120V). Airflow ratings are 23 CFM (651L/Min) average air volume. The combination of these factors means high performance.

MASTER HEAT GUN provides a fast flow of heated air for many applications.

### MASTER HEAT GUN

The number one choice of industry with rugged die-cast aluminum housing and powerful universal motor.



Renovation



Flooring



Roofing



Laboratory



Automotive



Shrink Wrap



Bend PVC



Heat pipes and more

- Activate adhesives and potting compounds
- Bend and form plastics and plastic laminates
- Cure and set adhesives
- Defrost freezers and frozen coils
- Dry conformal coatings on circuit boards
- General heating and drying applications

- Melt solder off the backs of printed circuit boards so thru hole components can be removed
- PVC bendings
- Preheat flux
- Remove dents in fiberglass
- Remove plastic autobody panels
- Remove windshield caulking

- Shrink and terminate environmental splices
- Shrink and terminate heat shrinkable insulated solder preforms
- Shrink heat shrinkable anti-static film
- Shrink heat shrinkable molded parts
- Shrink heavy gauge shrink-packaging
- Shrink wide heavy-wall and adhesive-lined tubing

- Spot dry paint fast
- Stretch vinyls
- Strip paint
- Thaw frozen pipes
- Hundreds of other uses

# MASTER HEAT GUN®

The number one Heat Gun choice of industry has a rugged die-cast aluminum housing for heavy duty use. Various models provide temperatures of 300°F/150°C, 500°F/260°C, 750°F/400°C or 1000°F/540°C.

*"Wherever fast, reliable flameless heat is the need"*

## Master Heat Gun features:

- High temperature and power ratings: up to 1000°F/540°C at 1740 watts
- High airflow rating: 23 CFM at 3000 FPM gets the job done fast
- Powerful high speed universal motor
- Sturdy die-cast aluminum housing
- Double protected heating element housing
- Easily replaceable, reinforced, mica-insulated ceramic heating element
- Externally accessible carbon brush holders for quick replacement
- Three position "OFF-COLD-HOT" rocker switch or optional "Momentary Contact Switch"
- Contoured, well balanced handle
- Non-slip rubber-backed base with 90° rotation
- 6 foot, 3-wire grounded cordset made with flexible, oil and sunlight resistant rubber jacket
- UL and CUL Listed. Assembled in USA
- Use to shrink tubing and packaging, bend plastics, cure adhesives, dry and heat parts, strip paint, defrost frozen pipes, heat sensitive materials, solder/desolder and more



Available in four temperature ranges see back page for details



Stable base for hands free use.



Rotating Stand



Master Heat Guns are available with optional "Momentary Contact Switch" for instant-off when the trigger is released. To order add "MC" suffix to model number. Example: HG-501A-MC



**Master Heat Gun Kits include:**  
Heat Gun, Reducer 51544, Spreader 51543, Reflector A-160-HG and Carrying Case 51013.

**Protect, store and carry your Master Heat Gun** and attachments in this rugged case. A well cared for Master Heat Gun will provide years of service. Durable construction along with user replaceable heating elements and motor brushes mean your heat gun will be ready for work.

# Master Heat Gun®

## Attachments & Accessories

Professional quality attachments & accessories provide the versatility to do more with your heat tool.



**A-160-HG**  
Shrink attachment for tubing up to 3/4"



**51543**  
2-1/4" Spreader attachment



**51544**  
7/8" Reducer attachment



**A-170-HG**  
Shrink attachment for tubing 3/4" to 2" O.D.



**30202**  
Solder preform attachment



**51309**  
3/8" Pinpoint attachment



**51542**  
Glass protector attachment



Get all 3!  
**35245**  
Three of our most popular attachments




**51013**  
Molded storage and carrying case

### ORDERING INFORMATION

MASTER HEAT GUN®								REPLACEMENT ELEMENT
MODEL NO.	DESCRIPTION							
HG-201A	200-300°F	93-150°C	120V	60 Hz	5A	600W	HAS-042K	
HG-301A	300-500°F	150-260°C	120V	60 Hz	12A	1440W	HAS-041K	
HG-501A	500-750°F	260-400°C	120V	60 Hz	14A	1680W	HAS-011K	
HG-751B	750-1000°F	400-540°C	120V	60 Hz	14.5A	1740W	HAS-043K	
HG-202A	200-300°F	93-150°C	220V	50 Hz	3A	600W	HAS-012K	
HG-302A	300-500°F	150-260°C	220V	50 Hz	6A	1440W	HAS-013K	
HG-502A	500-750°F	260-400°C	220V	50 Hz	7A	1680W	HAS-014K	
HG-752A	750-1000°F	400-540°C	220V	50 Hz	9A	1740W	HAS-016K	
MASTER HEAT GUN® KITS								REPLACEMENT ELEMENT
MODEL NO.	DESCRIPTION							
HG-201AK	200-300°F	93-150°C	120V	60 Hz	5A	600W	HAS-042K	
HG-301AK	300-500°F	150-260°C	120V	60 Hz	12A	1440W	HAS-041K	
HG-501AK	500-750°F	260-400°C	120V	60 Hz	14A	1680W	HAS-011K	
HG-751BK	750-1000°F	400-540°C	120V	60 Hz	14.5A	1740W	HAS-043K	



Replacement Heating Element



Brush, Spring and Cap Kit  
Part Number 35257



### Momentary Contact Switch:

An option for Master Heat Guns® Models. To order add "MC" suffix to model number. Example: HG-501A-MC.

Also, many international voltages/cordsets available upon request.

Contact our Sales Department for current certifications and appropriate model numbers.

### Specifications

- Air Volume: 23 CFM • Air Velocity: 3000 FPM
- Motor: Universal • Nozzle Opening: 1.2" I.D., 1.5" O.D.
- Cordset: 6 ft., 3-wire grounded • Dimensions: 9" L x 5.2" W x 10.1" H
- Net Weight Tool: 3.7 lbs. • Shipping Weight Tool: 5 lbs.
- Shipping Weight Kit: 10 lbs.

As with all electrical equipment and tools, for your safety, read the instruction manual before using.

All information including illustrations, is believed to be reliable. Users, however, should independently evaluate the suitability of this product for their application. The only obligations of Master Appliance are those in the Standard Terms and Conditions of Sale for this product. In no case will Master Appliance be liable for any incidental indirect, or consequential damages arising from the sale, resale, use or misuse of this product.

**MASTER**  
APPLIANCE  
Designers and Manufacturers of Heat Tools for Industry

USA  
MADE IN

FOR MASTER PRODUCTS CONTACT:

Master Appliance Corp. • 2420 18th St. • Racine, WI 53403 • Phone 800-558-9413 • Fax 262-633-9745

Web Site: www.masterappliance.com E-mail: sales@masterappliance.com

FORM# 58075 REV B