



# 7/8" MIN Power Series Size I Receptacles

3 & 4 Conductor MIN Power Series Size I Receptacles, 14AWG



Front Mount Receptacles | 1/2"-14 NPT Threads | Metric Threads | IP67 Rating



# of Poles	Male Faceview	Color Code	Wire AWG Rating	Mounting Threads	Male Receptacles	Female Receptacles
3	 7/8"-16UN2	<b>North American</b> 1. Green/Yellow 2. Black 3. White	<b>14 AWG</b>  600V 18A	1/2" NPT	MINH-3MR-**	MINH-3FR-**
				M16 x 1.5	MINH-3MR-**-M16	MINH-3FR-**-M16
				M20 x 1.5	MINH-3MR-**-M20	N/A
4	 7/8"-16UN2	<b>North American</b> 1. Black 2. White 3. Red 4. Green/Yellow	<b>14 AWG</b>  600V 15A	1/2" NPT	MINH-4MR-**	MINH-4FR-**
				M16 x 1.5	MINH-4MR-**-M16	MINH-4FR-**-M16
				M20 x 1.5	MINH-4MR-**-M20	N/A


D  
MIN Power Receptacles

\*\* Length in meters. 0.3m leads are standard. Longer lead lengths are available, please consult the factory for part numbers.

O-ring included on all metric threads. Lock nut included on lead length of 18" or more.


For 1/2" receptacles with lengths of 15" or longer O-ring and lock nut are included.

### 1/2"-14 NPT Threads




Male Receptacles

### M16 Threads




Male Receptacles


### M20 Threads



Male Receptacles



Female Receptacles



Female Receptacles

### Specifications:

Shell: Clear Anodized Aluminum  
 Insulator: 105°C, Oil Resistant Yellow PVC  
 Wire: 14 AWG: UL Style 1015, 600V

Contacts: Copper Alloy with Gold Plating  
 O-Ring: NBR  
 Temperature: -40°C to 105°C (-40°F to +221°F)