

# Field Stop Trench IGBT with Soft Fast Recovery Diode

## 120 A, 650 V

### AFGY120T65SPD

AFGY120T65SPD which is AEC Q101 qualified offers very low conduction and switch losses for a high efficiency operation in various applications, rugged transient reliability and low EMI.

Meanwhile, this part also offers an advantage of outstanding parallel operation performance with balance current sharing.

#### Features

- AEC-Q101 Qualified
- Very Low Saturation Voltage:  $V_{CE(Sat)} = 1.6\text{ V (Typ.) @ } I_C = 120\text{ A}$
- Maximum Junction Temperature:  $T_J = 175^\circ\text{C}$
- Positive Temperature Co-efficient for Easy Parallel Operating
- Tight Parameter Distribution
- High Input Impedance
- 100% of the Parts are Tested for  $I_{LM}$
- Short Circuit Ruggedness
- Co-packed with Soft Fast Recovery Diode

#### Typical Applications

- Traction Inverter for HEV/EV
- Auxiliary DC/AC Converters
- Motor Drives
- Other Power-Train Applications Requiring High Power Switch

#### MAXIMUM RATINGS

Rating	Symbol	Value	Unit
Collector-to-Emitter Voltage	$V_{CES}$	650	V
Gate-to-Emitter Voltage	$V_{GES}$	$\pm 20$	V
Transient Gate-to-Emitter Voltage		$\pm 30$	
Collector Current (Note 1)	@ $T_C = 25^\circ\text{C}$ @ $T_C = 100^\circ\text{C}$	$I_C$ 160 120	A
Pulsed Collector Current	$I_{LM}$	360	A
Pulsed Collector Current	$I_{CM}$	360	A
Diode Forward Current (Note 1)	@ $T_C = 25^\circ\text{C}$ @ $T_C = 100^\circ\text{C}$	$I_F$ 160 120	A
Maximum Power Dissipation	@ $T_C = 25^\circ\text{C}$ @ $T_C = 100^\circ\text{C}$	$P_D$ 714 357	W
Short Circuit Withstand Time @ $T_C = 25^\circ\text{C}$	SCWT	6	$\mu\text{s}$
Voltage Transient Ruggedness (Note 2)	dV/dt	10	V/ns
Operating Junction / Storage Temperature Range	$T_J, T_{STG}$	-55 to +175	$^\circ\text{C}$
Maximum Lead Temp. for Soldering Purposes, 1/8" from case for 5 seconds	$T_L$	265	$^\circ\text{C}$

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.



1. Value limit by bond wire
2.  $V_{CC} = 400\text{ V}$ ,  $V_{GE} = 15\text{ V}$ ,  $I_C = 360\text{ A}$ , Inductive Load




ON Semiconductor®

[www.onsemi.com](http://www.onsemi.com)

120 A, 650 V,  
 $V_{CESat} = 1.6\text{ V}$



#### MARKING DIAGRAM



\$Y = ON Semiconductor Logo  
&Z = Assembly Plant Code  
&3 = Date Code (Year & Week)  
&K = Lot Traceability Code  
AFGY120T65SPD = Specific Device Code

#### ORDERING INFORMATION

Device	Package	Shipping
AFGY120T65SPD	TO-247-3LD	30 Units / Tube

# AFGY120T65SPD

## THERMAL CHARACTERISTICS

Rating	Symbol	Value	Unit
Thermal resistance junction-to-case, for IGBT	$R_{\theta JC}$	0.21	°C/W
Thermal resistance junction-to-case, for Diode	$R_{\theta JC}$	0.32	
Thermal resistance junction-to-ambient	$R_{\theta JA}$	40	

## ELECTRICAL CHARACTERISTICS ( $T_J = 25^\circ\text{C}$ unless otherwise noted)

Parameter	Test Conditions	Symbol	Min	Typ	Max	Unit
-----------	-----------------	--------	-----	-----	-----	------

### OFF CHARACTERISTICS

Collector-emitter breakdown voltage, gate-emitter short-circuited	$V_{GE} = 0\text{ V}$ , $I_C = 1\text{ mA}$	$BV_{CES}$	650	-	-	V
Temperature Coefficient of Breakdown Voltage	$V_{GE} = 0\text{ V}$ , $I_C = 1\text{ mA}$	$\frac{\Delta BV_{CES}}{\Delta T_J}$	-	0.6	-	V/°C
Collector-emitter cut-off current, gate-emitter short-circuited	$V_{GE} = 0\text{ V}$ , $V_{CE} = 650\text{ V}$	$I_{CES}$	-	-	40	μA
Gate leakage current, collector-emitter short-circuited	$V_{GE} = 20\text{ V}$ , $V_{CE} = 0\text{ V}$	$I_{GES}$	-	-	±250	nA

### ON CHARACTERISTICS

Gate-emitter threshold voltage	$V_{GE} = V_{CE}$ , $I_C = 120\text{ mA}$	$V_{GE(th)}$	4.3	5.3	6.3	V
Collector-emitter saturation voltage	$V_{GE} = 15\text{ V}$ , $I_C = 120\text{ A}$ $V_{GE} = 15\text{ V}$ , $I_C = 120\text{ A}$ , $T_J = 175^\circ\text{C}$	$V_{CE(sat)}$	-	1.6	2.05	V
			-	2.15	-	

### DYNAMIC CHARACTERISTICS

Input capacitance	$V_{CE} = 30\text{ V}$ , $V_{GE} = 0\text{ V}$ , $f = 1\text{ MHz}$	$C_{ies}$	-	4930	-	pF
Output capacitance		$C_{oes}$	-	375	-	
Reverse transfer capacitance		$C_{res}$	-	42	-	
Internal Gate Resistance	$f = 1\text{ MHz}$	$R_G$	-	3	-	Ω
Gate charge total	$V_{CE} = 400\text{ V}$ , $I_C = 120\text{ A}$ , $V_{GE} = 15\text{ V}$	$Q_g$	-	125	187	nC
Gate-to-emitter charge		$Q_{ge}$	-	38	-	
Gate-to-collector charge		$Q_{gc}$	-	40	-	

### SWITCHING CHARACTERISTICS, INDUCTIVE LOAD

Turn-on delay time	$T_J = 25^\circ\text{C}$ , $V_{CC} = 400\text{ V}$ , $I_C = 120\text{ A}$ , $R_G = 5.0\ \Omega$ , $V_{GE} = 15\text{ V}$ , Inductive Load	$t_{d(on)}$	-	40	-	ns
Rise time		$t_r$	-	104	-	
Turn-off delay time		$t_{d(off)}$	-	80	-	
Fall time		$t_f$	-	116	-	
Turn-on switching loss		$E_{on}$	-	6.6	-	mJ
Turn-off switching loss		$E_{off}$	-	3.8	-	
Total switching loss		$E_{ts}$	-	10.4	-	
Turn-on delay time	$T_J = 175^\circ\text{C}$ , $V_{CC} = 400\text{ V}$ , $I_C = 120\text{ A}$ , $R_G = 5.0\ \Omega$ , $V_{GE} = 15\text{ V}$ , Inductive Load	$t_{d(on)}$	-	36	-	ns
Rise time		$t_r$	-	112	-	
Turn-off delay time		$t_{d(off)}$	-	92	-	
Fall time		$t_f$	-	160	-	
Turn-on switching loss		$E_{on}$	-	10.5	-	mJ
Turn-off switching loss		$E_{off}$	-	4.9	-	
Total switching loss		$E_{ts}$	-	15.4	-	

# AFGY120T65SPD

## ELECTRICAL CHARACTERISTICS ( $T_J = 25^\circ\text{C}$ unless otherwise noted) (Continued)

Parameter	Test Conditions	Symbol	Min	Typ	Max	Unit
<b>DIODE CHARACTERISTIC</b>						
Diode Forward Voltage	$I_F = 120\text{ A}, T_J = 25^\circ\text{C}$	$V_{FM}$	-	1.4	1.7	V
	$I_F = 120\text{ A}, T_J = 175^\circ\text{C}$		-	1.35	-	
Reverse Recovery Energy	$I_F = 120\text{ A}, dl_F/dt = 1000\text{ A}/\mu\text{s}, V_{CE} = 400\text{ V}, T_J = 25^\circ\text{C}$	$E_{rec}$	-	428	-	$\mu\text{J}$
	$I_F = 120\text{ A}, dl_F/dt = 1000\text{ A}/\mu\text{s}, V_{CE} = 400\text{ V}, T_J = 175^\circ\text{C}$		-	2026	-	
Diode Reverse Recovery Time	$I_F = 120\text{ A}, dl_F/dt = 1000\text{ A}/\mu\text{s}, V_{CE} = 400\text{ V}, T_J = 25^\circ\text{C}$	$T_{rr}$	-	107	-	ns
	$I_F = 120\text{ A}, dl_F/dt = 1000\text{ A}/\mu\text{s}, V_{CE} = 400\text{ V}, T_J = 175^\circ\text{C}$		-	203	-	
Diode Reverse Recovery Charge	$I_F = 120\text{ A}, dl_F/dt = 1000\text{ A}/\mu\text{s}, V_{CE} = 400\text{ V}, T_J = 25^\circ\text{C}$	$Q_{rr}$	-	2237	-	nC
	$I_F = 120\text{ A}, dl_F/dt = 1000\text{ A}/\mu\text{s}, V_{CE} = 400\text{ V}, T_J = 175^\circ\text{C}$		-	8155	-	

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

# AFGY120T65SPD

## TYPICAL CHARACTERISTICS




Figure 1. Typical Output Characteristics




Figure 2. Typical Output Characteristics




Figure 3. Typical Saturation Voltage




Figure 4. Transfer Characteristics




Figure 5. Saturation Voltage vs. Case Temperature




Figure 6. Saturation Voltage vs. Vge

# AFGY120T65SPD

## TYPICAL CHARACTERISTICS




Figure 7. Saturation Voltage vs.  $V_{CE}$




Figure 8. Saturation Voltage vs.  $V_{CE}$




Figure 9. Capacitance Characteristics




Figure 10. Gate Charge Characteristics




Figure 11. SOA Characteristics






Figure 12. Turn-On Characteristics vs. Gate Resistance

# AFGY120T65SPD


## TYPICAL CHARACTERISTICS




**Figure 13. Turn-Off Characteristics vs. Gate Resistance**




**Figure 14. Turn-On Characteristics vs. Collector Current**




**Figure 15. Turn-Off Characteristics vs. Collector Current**



**Figure 16. Switching Loss vs. Gate Resistance**



**Figure 17. Switching Loss vs. Collector Current**



**Figure 18. Forward Characteristics**

# AFGY120T65SPD

## TYPICAL CHARACTERISTICS




Figure 19. Reverse Current




Figure 20. Stored Charge




Figure 21. Reverse Recovery Time




Figure 22. Collector-to-Emitter Breakdown Voltage vs. Junction Temperature

TYPICAL CHARACTERISTICS




Figure 23. Transient Thermal Impedance of IGBT





Figure 24. Transient Thermal Impedance of Diode



# AFGY120T65SPD

## PACKAGE DIMENSIONS

TO-247-3LD  
CASE 340CU  
ISSUE A



DIM	MILLIMETERS		
	MIN	NOM	MAX
A	4.50	4.70	4.90
A1	2.10	2.40	2.70
A2	1.70	2.00	2.30
b	1.00	1.20	1.400
b2	2.20	2.40	2.60
b4	3.00	3.20	3.40
c	0.40	0.60	0.80
D	20.40	20.60	20.80
D1	15.47	15.67	15.87
D2	0.25	0.55	0.85
e	5.45 BSC		
E	15.40	15.60	15.80
E1	13.40	13.60	13.80
E2	4.12	4.30	4.52
L	19.70	20.00	20.30
L1	3.65	3.85	4.05
Q	5.35	5.55	5.75

**NOTES:**

- A. NO INDUSTRY STANDARDS APPLIES TO THIS PACKAGE.
- B. ALL DIMENSIONS ARE IN MILLIMETERS.
- C. DIMENSIONS ARE EXCLUSIVE OF BURRS, MOLD FLASH AND TIE BAR PROTRUSIONS.
- D. DRAWING CONFORMS TO ASME Y14.5-2009.

ON Semiconductor and are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at [www.onsemi.com/site/pdf/Patent-Marking.pdf](http://www.onsemi.com/site/pdf/Patent-Marking.pdf). ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor. "Typical" parameters which may be provided in ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights nor the rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor products for any such unintended or unauthorized application, Buyer shall indemnify and hold ON Semiconductor and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that ON Semiconductor was negligent regarding the design or manufacture of the part. ON Semiconductor is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

**PUBLICATION ORDERING INFORMATION**

LITERATURE FULFILLMENT:  
Email Requests to: [orderlit@onsemi.com](mailto:orderlit@onsemi.com)

TECHNICAL SUPPORT  
North American Technical Support:  
Voice Mail: 1 800-282-9855 Toll Free USA/Canada  
Phone: 011 421 33 790 2910

Europe, Middle East and Africa Technical Support:  
Phone: 00421 33 790 2910  
For additional information, please contact your local Sales Representative