



PANDUIT PART NUMBER	CONDUCTOR SIZE	STUD SIZE	OVERALL LENGTH "A" +/- .12	BARREL LENGTH "B" MIN	BARREL		TONGUE WIDTH "W" +/- .060	TONGUE THICKNESS "T" +/- .020	TONGUE LENGTH "P" MIN	HOLE OFFSET "G" +/- .031	STUD HOLE DIA "D" +/- .02	HOLE SPACING "S" +/- .04	WRENCH CLEARANCE "C" REF	WIRE STRIP LENGTH	PANDUIT DIE COLOR CODE PANDUIT DIE INDEX NUMBER (BURNDY DIE INDEX NUMBER)
					I.D. +/- .010	O.D. +/- .010									
LAB300-12-2	300 kcmil	1/2"	6.56	2.25	0.65	1.10	1.38	0.34	3.56	0.63	0.53	1.75	1.18	2-5/16"	BLUE DIE P76 (470)
LAB350-12-2R	350 kcmil	1/2"	6.56	2.31	0.72	1.11	1.52	0.38	3.56	0.63	0.53	1.75	1.18	2-5/16"	BROWN DIE P87(299)
LAB400-12-2	400 kcmil	1/2"	6.94	2.50	0.76	1.19	1.61	0.39	3.56	0.63	0.53	1.75	1.18	2-9/16"	GREEN DIE P94 (472)
LAB500-12-2R	500 kcmil	1/2"	7.31	3.00	0.84	1.32	1.74	0.45	3.56	0.63	0.53	1.75	1.18	3-1/16"	PINK DIE P99 (300)
LAB600-12-2	600 kcmil	1/2"	7.56	3.00	0.92	1.44	1.73	0.50	3.63	0.63	0.53	1.75	1.25	3-1/16"	BLACK DIE P106 (473)
LAB750-12-1R	750 kcmil	1/2"	8.25	3.44	1.03	1.59	1.74	0.54	3.63	0.63	0.53	1.75	1.25	3-7/16"	RED DIE P125 (301)
LAB800-12-1	800 kcmil	1/2"	8.31	3.38	1.06	1.66	1.75	0.59	3.63	0.63	0.53	1.75	1.25	3-7/16"	GRAY DIE P140 (474)
LAB1000-12-1	1000 kcmil	1/2"	9.73	4.50	1.19	1.84	2.56	0.63	3.63	0.63	0.53	1.75	1.25	4-3/4"	BROWN DIE P161 (302)

NOTES:

1. MATERIAL: SEAMLESS ALUMINUM TUBING, TIN PLATED
2. BARREL COLOR CODED WITH DIE SET INDEX NUMBER
3. WIRE TYPE:  
COPPER CLASS B CONCENTRIC, COMPRESSED AND COMPACT STRANDED WIRE  
COPPER CLASS C CONCENTRIC STRANDED WIRE  
ALUMINUM CLASS B, CONCENTRIC, COMPRESSED AND UNIDIRECTIONAL LAY COMPACT STRANDED WIRE
4. UL LISTED & CSA CERTIFIED TEMPERATURE RATED 90° C (AL9CU)
5. UL LISTED & CSA CERTIFIED VOLTAGE RATING 35 KV
6. ALL DIMENSIONS IN INCHES



REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
10	5/18	JHNU	JHNU	RGB	REVISED TONGUE WIDTH FOR LAB400-12-2: 1.61 WAS 1.66	N41152BA-C41152

TITLE LAB SERIES 300kcmil - 1000 kcmil ALUMINUM LUGS CUSTOMER DRAWING		<b>PANDUIT</b>
ITEM REVISION NAME	N41152BA-C41152/10	
DATASET FILE NAME	C41152/10.SLDDRW	MATERIAL SEE NOTES
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm] .X ± .XXX ± .XX ± ANGLES ±		
DRAWN BY	DATE	DRAWING NUMBER
MS	4/95	C41152
CHK	SCALE	SHEET 1 OF 1
	NONE	SIZE B