

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (http://phoenixcontact.com/download)



Inline digital output terminal, complete with accessories (connector and labeling field), 4 relay contacts, 5 - 253 V AC, 10 A, high inrush current

#### Product description

The terminal is designed for use within an Inline station. It has four floating relay contacts. The terminal can be used in the SELV area and in the AC area. Observe the appropriate regulations and safety notes when using the terminal in the AC area. Features

- Safe isolation according to EN 50178
- Floating connection for four actuators
- Nominal current at the output: 10 A
- High inrush current
- Diagnostic and status indicators

#### **Product Features**

- Mominal current 10 A
- ☑ Safe isolation
- Diagnostic and status indicators

## Key commercial data

Packing unit	1 pc
Weight per Piece (excluding packing)	260.0 GRM
Custom tariff number	85389091
Country of origin	Germany

#### Technical data

#### Note

I Utilization restriction	EMC: class A product, see manufacturer's declaration in the download area
---------------------------	---

#### **Dimensions**

Width	48.8 mm
Height	119.8 mm



## Technical data

## Dimensions

Depth	71.5 mm
Note on dimensions	Housing dimensions

#### Ambient conditions

Ambient temperature (operation)	-25 °C 55 °C
Ambient temperature (storage/transport)	-25 °C 85 °C
Permissible humidity (operation)	0 % 85 % (non-condensing)
Permissible humidity (storage/transport)	0 % 85 % (slight temporary condensation may sometimes appear on the housing)
Air pressure (operation)	80 kPa 106 kPa (up to 2000 m above sea level)
Air pressure (storage/transport)	70 kPa 106 kPa (up to 3000 m above sea level)
Degree of protection	IP20

#### General

Weight	229 g
Note on weight specifications	with connectors
Mounting type	DIN rail
Protection class	III, IEC 61140, EN 61140, VDE 0140-1
Test section	Relay contact / Bus logics 4 kV 50 Hz 1 min
	Contact to contact 1 kV 50 Hz 1 min
	Contact / PE 1 kV 50 Hz 1 min

#### Interfaces

Designation	Inline local bus
Connection method	Inline data jumper
Transmission speed	500 kBit/s

## Power supply for module electronics

Supply voltage	24 V DC (nominal value)
Supply voltage range	19.2 V DC 30 V DC (including all tolerances, including ripple)
Communications power U <sub>L</sub>	7.5 V (via voltage jumper)
Current consumption	max. 34 mA (from the local bus)

## Inline potentials

Communications power U <sub>L</sub>	7.5 V
Current consumption from U <sub>L</sub>	max. 34 mA
Current consumption from U <sub>ANA</sub>	10 mA (Maximum 55 mA during the switching process (duration of approximately 25 ms per switched relay))

## Digital outputs

Output name	Relay output



## Technical data

## Digital outputs

Connection method	Spring-cage connection
	Floating SPDT relay contact
Number of outputs	4
Maximum output current per channel	10 A

#### Classifications

## eCl@ss

eCl@ss 4.0	27250302
eCl@ss 4.1	27250302
eCl@ss 5.0	27250302
eCl@ss 5.1	27242604
eCl@ss 6.0	27242604
eCl@ss 7.0	27242604
eCl@ss 8.0	27242604

#### **ETIM**

ETIM 2.0	EC001430
ETIM 3.0	EC001599
ETIM 4.0	EC001599
ETIM 5.0	EC001599

## **UNSPSC**

UNSPSC 6.01	43172015
UNSPSC 7.0901	43201404
UNSPSC 11	43172015
UNSPSC 12.01	43201404
UNSPSC 13.2	43201404

#### Accessories

Accessories

Connector set



#### Accessories

Connector set - IB IL DOR LV-PLSET - 2742667



Connector set for distance terminal

#### Distance terminal

Inline terminal - IB IL DOR LV-SET - 2742641



Inline distance terminal, without accessories

## Labeling panel

Labeling field - IB IL FIELD 2 - 2727501

Labeling field, width: 12.2 mm



Labeling field - IB IL FIELD 8 - 2727515

Labeling field, width: 48.8 mm



Plug



#### Accessories

Inline connector - IB IL SCN-8-AC-REL - 2740290



Plug, for digital 1, 2 or 8-channel Inline terminals with AC voltage

#### Terminal marking

Insert strip - ESL 62X10 - 0809492



Insert strip, Sheet, white, unlabeled, can be labeled with: Office printing systems, Plotter: Laser printer, Mounting type: Insert, Lettering field: 62 x 10 mm

Insert strip - ESL 62X46 - 0809502



Insert strip, Sheet, white, unlabeled, can be labeled with: Office printing systems, Plotter: Laser printer, Mounting type: Insert, Lettering field:  $62 \times 46 \text{ mm}$ 

Phoenix Contact 2014 © - all rights reserved http://www.phoenixcontact.com