


REVISIONS			
LTR	DESCRIPTION	DATE	APPROVED
B	REVISED AND REDRAWN PER ECN T-17680	92 Aug 12	[Signature]
C	REVISE PER DCR# T-22768	4/16/99	M.HIGGY



NOTES:

- 1. Δ MTC100-JH1-XXX OR MTC100-JH2-XXX (SEE RAYCHEM INFORMATION DRAWING D-659-0097 AND HOUSING SCD's FOR FURTHER DETAILS).
- 2. USE MIL-C-38999 SERIES 2 SIZE 16 CONTACTS OR EQUIVALENT. REFERENCE D-659-0097 FOR INSERTION/REMOVAL TOOLS. SEALING PLUGS AND CRIMP TOOLS WHEN APPLICABLE. THESE COMPONENTS ARE TO BE ORDERED SEPARATELY.
- 3. GROMMET DESIGNED TO SEAL ON WIRES HAVING AN INSULATION DIAMETER OF .065 IN. (1.65mm) TO .109 IN. (2.77mm).
- 4. PERFORMANCE: THIS PRODUCT MEETS THE REQUIREMENTS OF RAYCHEM SPECIFICATION C-6115.
- 5. MATERIALS:

A) PLASTIC INSERT	HIGH GRADE POLYARYLENE THERMOPLASTIC
B) GROMMET	FLUOROSILICONE PER MIL-R-25988
C) INTERFACIAL SEAL	FLUOROSILICONE PER MIL-R-25988
D) RETENTION CLIP	BERYLLIUM COPPER 172 PER QQ-C-533

Δ WEIGHT: 0.0095 lbs [4.300 Grams] MAXIMUM.

If this document is printed it becomes uncontrolled.
Check with the web for latest revision.

SPECIFICATION CONTROL DRAWING

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES. METRIC DIMENSIONS ARE IN BRACKETS. DECIMALS .XXX ± [mm] .XX ± [mm] ANGLES .X ± WEIGHT: Δ	REDRAWN	PIQUE'	92AUG10	Raychem <small>RAYCHEM CORPORATION 300 CONSTITUTION DRIVE MENLO PARK, CALIFORNIA 94025</small>
	ORG. DRW	ALEXANDER	84OCT24	
	CHECKED	J. BLAIR	84OCT24	
	APPROVED	J. CAMERON	84OCT24	
CAD NAME: T22768.TIF				TITLE INSERT, SOCKET PRIMARY 5 NUMBER 16 CAVITIES POWER BLOCK CONNECTOR TEMPERATURE RATING 125°C MTC SERIES
THIRD ANGLE PROJECTION			SIZE B CODE IDENT. NO. 06090 DWG. NO. MTCP-116-05S1 REV C	
DO NOT SCALE THIS DRAWING			SHEET 1 OF 1	