

LS45M21B11



LS45M21B11 Limit Switch



General Information

Extended Product Type	LS45M21B11
Product ID	1SBV013121R1211
EAN	3471522612953
Catalog Description	LS45M21B11 Limit Switch
Long Description	LS45M21B11 Limit Switch

Ordering

EAN	3471522612953
Minimum Order Quantity	10 piece
Customs Tariff Number	85364900

Dimensions

Product Net Width	40 mm
Product Net Weight	0.26 kg

Container Information

Package Level 1 Units	1 piece
Package Level 1 Width	140 mm
Package Level 1 Height	70 mm
Package Level 1 Depth / Length	45 mm
Package Level 1 Gross Weight	0.26 kg
Package Level 1 EAN	3471522612953
Package Level 2 Units	10 piece
Package Level 2 Gross Weight	2.6 kg

Environmental

Ambient Air Temperature	Operation -25 ... +70 °C Storage -30 ... +80 °C
Resistance to Vibrations acc. to IEC 60068-2-6	25g (10 to 500 Hz) no change in position of contacts greater than 100 µs
Resistance to Shock acc. to IEC 60068-2-27	Half-sine Pulse for 11 ms, No Change in Contact Position 50 m/s ²
RoHS Status	Following EU Directive 2011/65/EU

Technical UL/CSA

Pilot Duty of Contact Elements acc. UL508

A600
Q600

Additional Information

Action Type of the Contact Element (acc. to IEC 60947-5-1 snap action contacts 5-1)

Actuator Type	stainless steel lateral plain plunger
Actuating Force	Minimum Force acc. to IEC 60947-5-1 30 NEW
Actuation Speed	acc. to IEC 60947-5-1 Max. 0.50 MTS acc. to IEC 60947-5-1 Min. 0.00 MTS
Angular Head Adjustment	adjustable head every 90°
Angular Lever Adjustment	none
Climatic Withstand	according to IEC 68-2-3 and salty mist according to IEC 68-2-11
Conventional Free-air Thermal Current (I_{th})	acc. to IEC 60947-5-1, $q = 40$ °C 10 A
Connecting Capacity	Bar AWG 20 ... AWG 14 Bar 0.5 ... 2.5
Consistency (Measured over 1 Million Operations)	0.05 mm
Contact Element Form (acc. to IEC 60947-5-1)	Zb
Connecting Terminals (delivered in open position)	M3.5 (+,-) pozidriv 2 screw with cable clamp
Degree of Protection	acc. to IEC 60529 IP66
Electrical Shock Protection acc. to IEC 536	Class I
Maximum Electrical Switching Frequency	3600 cycles per hour AC-15 3600 cycles per hour DC-13 3600 cycles per hour
Mounting by Screws (not supplied)	2 or 4 x M5 screws
Mounting Position	all positions are authorised
Movement to be Detected	on end
Number of Auxiliary Contacts NC	1
Number of Auxiliary Contacts NO	1
Number and Type of Bottom Cable Glands	1/2 NPT cable gland
Operating Head Shape	F shape acc. EN 50041
Order Multiple	1 piece
Positive Opening Operation Force (Direct Opening Action)	Minimum Force acc. to IEC 60947-5-1 70 NEW
Positive Opening Operation of NC Contact(s)	Yes
Product Main Type	LS40
Product Name	Limit Switch
Rated Frequency (f)	Supply Circuit 50 60 Hz
Rated Impulse Withstand Voltage (U_{imp})	6 kV
Rated Insulation Voltage (U_i)	acc. to UL/CSA 600 V acc. to IEC 60947-5-1 and VDE 0110 (Gr. C) 500 V
Rated Operational Current AC-15 (I_{θ})	(230 V AC) 3.1 A (240 V) 3 A (400 V) NC 4 A (130 V) 5.5 A (24 V) 10 A
Rated Operational Current DC-13 (I_{θ})	(125 V) 0.55 A (24 V) 6 A (250 V) 0.4 A (110 V) 0.6 A

Resistance Between Contacts	25 E45
RoHS Date	20171115
Standards	IEC 60947-1, IEC 60947-5-1, EN 60947-1, EN 60947-5-1, UL 508 and CSA C22-2 N°14
Terminal Marking	according to EN 50013
Terminal for Protective Conductor	M 3.5 (+,-) pozidriv 2 screw with cable clamp

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	AC1300
Declaration of Conformity - CE	1SBD250883U1000
Environmental Information	1SBD250102E1000
Instructions and Manuals	AC1300
RoHS Information	1SBD250883U1000

Classifications

ETIM 4	EC001829 - Position switch modular
ETIM 5	EC001829 - Position switch modular
ETIM 6	EC000030 - End switch
ETIM 7	EC000030 - End switch
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)

Categories

Low Voltage Products and Systems → Control Products → Sensors → Limit Switches

