

PRODUCT-DETAILS

OT400U04

OT400U04 SWITCH-DISCONNECTOR



General Information

| | |
|-----------------------|---|
| Extended Product Type | OT400U04 |
| Product ID | 1SCA022748R1060 |
| EAN | 6417019242798 |
| Catalog Description | OT400U04 SWITCH-DISCONNECTOR |
| Long Description | 4-pole, front operated, base mounted non-fusible disconnect switch, handle and shaft are not included, terminal bolt kit included |

Ordering

| | |
|------------------------|--------------|
| Minimum Order Quantity | 1 piece |
| Customs Tariff Number | 85365080 |
| Country of Origin | Finland (FI) |

Popular Downloads

| | |
|-----------------------------------|--|
| Data Sheet, Technical Information | 1SCC301020C0201 |
| Instructions and Manuals | 1SCC301035M0019 |
| Mechanical Drawings | 1SCC301264F0002 1SCC301263F0002 OT400U04.igs |

Dimensions

| | |
|----------------------------|------------------|
| Product Net Width | 275 mm |
| Product Net Height | 220 mm |
| Product Net Depth / Length | 105 mm |
| Product Net Weight | 3.8 kg 8.3 lb |

Technical

| | |
|--|--|
| Rated Operational Current AC-22A (I_e) | (380 ... 415 V) 400 A (500 V) 400 A (690 V) 400 A |
| Rated Operational Current AC-23A (I_e) | (380 ... 415 V) 400 A (500 V) 400 A (690 V) 400 A |
| Rated Operational Power AC-23A (P_e) | (380 ... 415 V) 220 kW (500 V) 280 kW (690 V) 400 kW |
| Conventional Thermal Current (I_{the}) | Fully Enclosed 400 A |
| Rated Impulse Withstand Voltage (U_{imp}) | 12 kV |
| Rated Insulation Voltage (U_i) | acc. to IEC/EN 60664-1 1000 V |
| Rated Operational Voltage | Main Circuit 1000 V |
| Rated Short-Circuit Making Capacity (I_{cm}) | (690 V) 65 kA |
| Rated Short-time Withstand Current (I_{cw}) | for 1 s 15 kA |
| Power Loss | at Rated Operating Conditions per Pole 10 W |
| Pollution Degree | 3 |
| Handle Type | Handle and shaft not included |
| Fourth Pole Position | Right Side |
| Fourth Pole Type | Switched - Simultaneous Function |
| Switches Operating Mechanism | Mechanism at the End of the Switch 04 (Left Side) |
| Distance Between Phases | Standard |
| Position of Line Terminals | Top In - Bottom Out Bottom In - Top Out |
| Operating Mode | Front operated |
| Standards | IEC 60947-3 / UL 98 / CSA C22.2 NO.4 |
| Special Functions | No |
| Mounting Type | Base mounting |
| Number of Poles | 4 |
| Degree of Protection | Front IP00 |
| Terminal Type | Lug terminals |
| Tightening Torque | acc. IEC 60947-1 42.4 N·m |
| Mechanical Durability | 16000 |
| Lock Type | No |

Technical UL/CSA

| | |
|----------------------------------|--|
| Maximum Operating Voltage UL/CSA | 600 V |
| Horsepower Rating UL/CSA | (acc. to UL 200 V) 100 Hp (acc. to UL 208 V) 100 Hp |

(acc. to UL 240 V) 125 Hp
 (acc. to UL 480 V) 250 Hp
 (acc. to UL 600 V) 350 Hp

| | |
|-----------------------------|-----------|
| Ampere Rating UL/CSA | 400 A |
| Tightening Torque UL/CSA | 375 in-lb |

Environmental

| | |
|------------------------------|-----------------------------------|
| RoHS Status | Following EU Directive 2011/65/EU |
| Environmental Information | 1SCC301149D0202 |

Certificates and Declarations (Document Number)

| | |
|-----------------------------------|-----------------|
| Declaration of Conformity - CE | 1SCC301135D2704 |
| Environmental Information | 1SCC301149D0202 |
| Instructions and Manuals | 1SCC301035M0019 |
| RoHS Information | 1SCC301149D0203 |

Container Information

| | |
|-----------------------------------|-------------------|
| Package Level 1 Units | box 1 piece |
| Package Level 1 Width | 250 mm 9.8 in |
| Package Level 1 Depth / Length | 290 mm 11.4 in |
| Package Level 1 Height | 170 mm 6.7 in |
| Package Level 1 Gross Weight | 4.1 kg 9 lb |
| Package Level 1 EAN | 6417019242798 |

Classifications

| | |
|-------------------------------|--|
| Object Classification Code | Q |
| ETIM 5 | EC000216 - Switch disconnecter |
| ETIM 6 | EC000216 - Switch disconnecter |
| ETIM 7 | EC000216 - Switch disconnecter |
| UNSPSC | 39122233 |
| WEEE Category | 5. Small Equipment (No External Dimension More Than 50 cm) |

Categories

Low Voltage Products and Systems → Switches → Switch Disconnectors

