

## VMAXAA Product Details



**VMAXAA**  
(3-1437466-3)

TE Internal Number: 3-1437466-3

 [Active](#)

### Sensors & Protective Relays

[Not EU RoHS or ELV Compliant](#)

#### Product Highlights:

- Relay Type = Protective Relay
- VMA Series
- Pick-Up = 104 V
- Drop-Out = 78 - 99 V
- AC Actuating System

[View all Features](#)

### Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

[Add to My Part List](#)
 [Request Sample](#)
 [Find Similar Products](#)
 [Buy Product](#)

### Documentation & Additional Information

#### Product Drawings:

- None Available

#### Catalog Pages/Data Sheets:

- None Available

#### Product Specifications:

- None Available

#### Application Specifications:

- None Available

#### Instruction Sheets:

- None Available

#### CAD Files:

- None Available

#### Additional Information:

- [Product Line Information](#)

#### Related Products:

- [Tooling](#)

### Product Features (Please use the Product Drawing for all design activity)

#### Product Type Features:

- Termination Type = 8 Pin Octal-Style Plug

#### Electrical Characteristics:

- [Actuating System](#) = AC
- Input Voltage (VAC) = 120
- [Phase](#) = Single
- Contact Rating = 7A @ 250 VAC

#### Body Related Features:

- [Series](#) = VMA

#### Contact Related Features:

- [Relay Type](#) = Protective Relay
- [Mode of Operation](#) = Fixed Pick-Up and Adjustable Drop-Out
- Approx. Dimensions (L x W x H) (mm [in]) = 49.00 x 49.00 x 83.00 [1.930 x 1.930 x 3.270]
- Mounting Options = Socket
- Type of Control = Locking Potentiometer

#### Housing Related Features:

- [Pick-Up \(V\)](#) = 104
- [Drop-Out \(V\)](#) = 78 - 99

#### Configuration Related Features:

- [Contact Arrangement](#) = 2 Form C, DPDT, 2 C/O
- [Contact Arrangement, Additional Output](#) = None

#### Industry Standards:

- [RoHS/ELV Compliance](#) = Not ELV/RoHS compliant
- [Lead Free Solder Processes](#) = Not suitable for lead free processing
- Approved Standards = UL Recognized, CE Approved

#### Conditions for Usage:

- Temperature Range (°C) = -10 - +55

#### Operation/Application:

- [Protection Function](#) = Undervoltage, Close Differential
- [Time Delay](#) = Without

#### Other:

- Brand = Agastat

 [BOOKMARK](#)   

### Corporate Information

[Who We Are](#)  
[Investors](#)  
[News Room](#)  
[Supplier Portal](#)  
[Careers](#)

### Quick Links

[Check Distributor Inventory](#)  
[Cross Reference](#)  
[Find Documents & Drawings](#)  
[Product Compliance Support Center](#)  
[Site Map](#)

### Customer Support

[Email or Chat with Us](#)  
[Find a Phone Number](#)  
[Search Knowledge Base](#)  
[Manage Your Account](#)

### Sign up for our eNewsletter

Enter your email address

Follow us on: 