

SCERX22ABA Product Details

[Share](#) [Print](#) [Email](#)


SCERX22ABA
(2-1437463-1)

TE Internal Number: 2-1437463-1

Active

Time Delay Relays

Not EU RoHS or ELV Compliant

Product Highlights:

- SCE Specification Grade True Off-Delay Timing Series
- Input Voltage = 120 VAC
- Input Voltage = 125 VDC
- Contact - Arrangement = 2 Form C, DPDT, 2 C/O
- Contact Rating = 5A Resistive @ 120/240 VAC

[View all Features](#)

Quick Links

- ▶ [Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

[Add to My Part List](#) [Request Sample](#) [Find Similar Products](#) [Buy Product](#)

Documentation & Additional Information	
<p>Product Drawings:</p> <ul style="list-style-type: none"> • None Available <p>Catalog Pages/Data Sheets:</p> <ul style="list-style-type: none"> • None Available <p>Product Specifications:</p> <ul style="list-style-type: none"> • None Available <p>Application Specifications:</p> <ul style="list-style-type: none"> • None Available <p>Instruction Sheets:</p> <ul style="list-style-type: none"> • None Available <p>CAD Files:</p> <ul style="list-style-type: none"> • None Available 	<p>Additional Information:</p> <ul style="list-style-type: none"> • Product Line Information <p>Related Products:</p> <ul style="list-style-type: none"> • Tooling

Product Features (Please use the Product Drawing for all design activity)	
<p>Mechanical Attachment:</p> <ul style="list-style-type: none"> • Mounting Options = Socket <p>Electrical Characteristics:</p> <ul style="list-style-type: none"> • Input Voltage (VAC) = 120 • Input Voltage (VDC) = 125 • Contact Rating = 5A Resistive @ 120/240 VAC <p>Termination Features:</p> <ul style="list-style-type: none"> • Termination Type = 8-Pin Octal Style Plug <p>Dimensions:</p> <ul style="list-style-type: none"> • Approx. Dimensions (L x W x H) (mm [in]) = 50.00 x 50.00 x 83.00 [1.970 x 1.970 x 3.270] <p>Contact Features:</p> <ul style="list-style-type: none"> • Delay Time = 0.5 seconds to 15 seconds • Type of Control = Knob • Repeatability, Max. = ± 1% 	<p>Configuration Features:</p> <ul style="list-style-type: none"> • Contact - Arrangement = 2 Form C, DPDT, 2 C/O • Multiple Timing Ranges = Without <p>Industry Standards:</p> <ul style="list-style-type: none"> • Approved Standards = CE Approved, CSA Certified, UL Recognized • RoHS/ELV Compliance = Not ELV/RoHS compliant • Lead Free Solder Processes = Not suitable for lead free processing <p>Conditions for Usage:</p> <ul style="list-style-type: none"> • Temperature Range (°C) = -30 - +65 <p>Operation/Application:</p> <ul style="list-style-type: none"> • Mode of Operation = True Off-Delay <p>Other:</p> <ul style="list-style-type: none"> • Series = SCE Specification Grade True Off-Delay Timing • Brand = Agastat

Corporate Information

- [About TE](#)
- [Investors](#)
- [News Room](#)
- [Supplier Portal](#)
- [Careers](#)
- [Terms & Conditions](#)
- [Privacy Policy](#)

Quick Links

- [Distributor Inventory](#)
- [Product Cross Reference](#)
- [Documents & Drawings](#)
- [Product Compliance Support Center](#)
- [Site Map](#)

Customer Support

- [Email or Chat With Us](#)
- [Find a Phone Number](#)
- [Knowledge Base](#)
- [Manage Your Account](#)

Keep Me Informed



Feedback