


A 11mm wide potentiometer for audio, visual, electronic musical instruments and various applications.



Typical Specifications

Items	Specifications
Total resistance tolerance	± 20%
Maximum operating voltage	50V AC, 20V DC
Total rotational angle	300 ± 5°
Rotational torque	3 to 20mN · m
Operating life	15,000cycles
Operating temperature range	- 10°C to + 70°C

Product Line

Number of resistor elements	Mounting direction	Bushing	Shaft type	Length of the shaft (LM ₁) (mm)	Center detent	Total resistance (kΩ)	Resistance taper	Minimum order unit (pcs.)		Products No.	Drawing No.	
								Japan	Export			
Single-unit (20V DC)	Vertical type	Without	Flat	15	Without	10	1B	1,200	2,400	RK11K1130A2X	2	
				20	With			1,000	2,000	RK11K1130A0M RK11K1130040		
				25	Without			800	1,600	RK11K1130A07 RK11K113002F		
		With		20	With	10		1,000	2,000	RK11K114003Y RK11K1140A9L		
				22.5	Without			800	1,600	RK11K1140A23 RK11K114001Z		
				25	With					RK11K1140A3L RK11K1140A4Q RK11K1140A2S		
				27.5	Without					20		4
				30						10		
				32.5						10		
	Horizontal type	Without	25	15A	800	1,600	RK11K1110A3D			1		
		With	22.5		With	1,000	2,000	RK11K1120060	3			
			25		Without	10	800	1,600		RK11K1120A5T RK11K1120A31		
	27.5	Without	20									

Notes

1. Other varieties are also available. Refer to "Other Specifications" (P.339).
2. Nut and washer are not attached. Please specify if required.

Packing specifications

Tray

Length of the shaft LM ₁ (mm)	Number of packages (pcs.)		Export package measurements (mm)
	1 case / Japan	1 case / export packing	
15	1,200	2,400	374 × 532 × 240
20 to 22.5	1,000	2,000	
25 or more	800	1,600	

Refer to P.339 for other specifications.
Refer to P.340 for ordering products not listed.
Refer to P.349 for soldering conditions.

Dimensions

Unit:mm

Rotary
Potentiometers
Slide
Potentiometers

Metal
Shaft
Insulated
Shaft
Knob
Operating
Ring Type

No.	Photo	Style	PC board mounting hole dimensions (Viewed from mounting side)																					
1																								
2		<table border="1"> <tr> <td>LM₁</td> <td>15</td> <td>20</td> <td>25</td> </tr> <tr> <td>ℓ₁</td> <td>4.5</td> <td>7</td> <td>12</td> </tr> </table>	LM ₁	15	20	25	ℓ ₁	4.5	7	12														
LM ₁	15	20	25																					
ℓ ₁	4.5	7	12																					
3		<table border="1"> <tr> <td>LM₁</td> <td>22.5</td> <td>25</td> <td>27.5</td> </tr> <tr> <td>L₁</td> <td>15</td> <td>17.5</td> <td>20</td> </tr> <tr> <td>ℓ₁</td> <td>7</td> <td>12</td> <td>12</td> </tr> </table>	LM ₁	22.5	25	27.5	L ₁	15	17.5	20	ℓ ₁	7	12	12										
LM ₁	22.5	25	27.5																					
L ₁	15	17.5	20																					
ℓ ₁	7	12	12																					
4		<table border="1"> <tr> <td>LM₁</td> <td>20</td> <td>22.5</td> <td>25</td> <td>27.5</td> <td>30</td> <td>32.5</td> </tr> <tr> <td>L₁</td> <td>12.5</td> <td>15</td> <td>17.5</td> <td>20</td> <td>22.5</td> <td>25</td> </tr> <tr> <td>ℓ₁</td> <td>7</td> <td>7</td> <td>12</td> <td>12</td> <td>12</td> <td>12</td> </tr> </table>	LM ₁	20	22.5	25	27.5	30	32.5	L ₁	12.5	15	17.5	20	22.5	25	ℓ ₁	7	7	12	12	12	12	
LM ₁	20	22.5	25	27.5	30	32.5																		
L ₁	12.5	15	17.5	20	22.5	25																		
ℓ ₁	7	7	12	12	12	12																		

11mm Size Insulated Shaft Snap-in Type Potentiometer / Other Specifications

In addition to the products listed, we can accommodate the follow specifications.

Total Resistance Variety

Total resistance (kΩ)	5	10	20	50	100	200
-----------------------	---	----	----	----	-----	-----

Resistance Taper

Resistance taper	15A	1B	3B	15C
------------------	-----	----	----	-----

Tapped Types are Also Available

RK11K (single-unit) is also available with tap.

Shaft Variety

Unit:mm

Style	Without bushing				With bushing						
	Horizontal type		Vertical type		Horizontal type		Vertical type				
Shaft variety	LM ₁	15	20	25	30	20	22.5	25	27.5	30	32.5
	L ₁	—	—	—	—	12.5	15	17.5	20	22.5	25
	ℓ ₁	4.5	7	12	12	7	7	12	12	12	12
	LB	—	—	—	—	5	5	5	5	5	5

Detail dimensions			
-------------------	--	--	--

Terminal Layout / Circuit Diagram

<p>Without tap</p>	<p>With tap</p>
---------------------------	------------------------

Note

marked are specifications recommended by Alps.

Rotary Potentiometers

Slide Potentiometers

Metal Shaft

Insulated Shaft

Knob Operating

Ring Type

11mm Size Insulated Shaft Snap-in Type Potentiometer / Ordering Products Not Listed

When ordering product varieties that are not listed, specify referring to the examples below.

Rotary Potentiometers
Slide Potentiometers

Metal Shaft
Insulated Shaft
Knob Operating
Ring Type

Sample Part Number



Model type

Code	Model type
1	Horizontal type without bushing
2	Horizontal type with bushing
3	Vertical type without bushing
4	Vertical type with bushing

Shaft type

Code	Shaft type
F	Flat

* Only available in flat format.

Length of the shaft (LM₁) (mm)

Code	Length of the shaft	Code	Length of the shaft
15	15	25	25
20	20	30	30
22	22.5	32	32.5
27	27.5		


Detent

Code	Center detent
C0	Without
C1	With

Resistance taper

Code	Resistance taper	Code	Resistance taper
A	15A	C	15C
B	1B	V	3B

B: For tone & general
V: For vol.



Total resistance

Code	Total resistance (kΩ)	Code	Total resistance (kΩ)
502	5	503	50
103	10	104	100
203	20	204	200

Note

marked are specifications recommended by Alps.

Insulated Shaft Potentiometers

List of Varieties

Type	9mm Size			11mm Size	12mmSize		14mm Size	
Series	RK09K11 RK09D11	RK09K12	RK09Y11L	RK11K	RK12L12	RK12L115	RK14K	
	Single-unit	Dual-unit	Single-unit		Dual-unit	Dual-unit	Dual-unit	
Photo								
Terminal mounting	Vertical / Horizontal		Horizontal	Vertical / Horizontal		Vertical	Vertical / Horizontal	
Bushing	Without			With/ Without	Without	With	With/ Without	
Operating temperature range	- 10°C to + 70°C					- 40°C to + 85°C	- 10°C to + 70°C	
Operating life	5,000 cycles	10,000 cycles	1,000,000 cycles	15,000cycles				
Available for automotive use	—	—	—	—	—	●	—	
Life cycle (availability)	★ ₂		★ ₂	★ ₂	★ ₂	★ ₂		
Electrical performance	Total resistance (kΩ)	5, 10, 20, 50, 100, 200		10	5, 10, 20, 50, 100, 200		5, 10, 20, 50, 100	5, 10, 20, 50, 100, 200
	Resistance taper	15A, 1B, 3B, 15C		1B	15A, 1B, 3B, 15C		15A, 1B, 3B	15A, 1B, 3B, 15C
	Total resistance tolerance	± 20%	± 30%		± 20%			
	Rated power	0.05W	0.03W	0.01W	0.05W			
	Maximum operating voltage	50V AC 20V DC	50V AC For AC only	50V AC 5V DC	50V AC 20V DC	50V AC For AC only	50V AC 20V DC	50V AC For AC only
	Gang error	—	- 40dB to 0dB 3dB max.	—	—	Volume control - 40dB to 0dB 3dB max. For tone control within 2dB at center	—	Volume control - 40dB to 0dB 3dB max. For tone control within 2dB at center
	Insulation resistance	100MΩ min. 250V DC			100MΩ min. 500V DC	100MΩ min. 250V DC		
	Voltage proof	250V AC for 1 minute			500V AC for 1 minute	300V AC for 1 minute		
	Center-taps	Without			With/ Without	Without		With/Without (Volumecontrol)
	Mechanical performance	Detent	Without, Center		Without	Without, Center		Custom
Stopper strength		0.3N·m		—	Without bushing 0.3N·m With bushing 0.6N·m	0.5N·m		0.6N·m
Push-pull strength		50N max.		30N max.	80N max.			
Vibration		10 to 55 to 10Hz/min., the amplitude is 1.5mm for all the frequencies, in the 3 direction of X, Y and Z and for 2 hours respectively						
Shaft configuration	Flat type, Knob type, Screwdriver type			Flat type				
Terminal style	Insertion							
Page	330		336	337	341	344	345	

● Insulated Shaft Potentiometers Soldering Conditions	349
● Potentiometers Cautions	404
● Potentiometers Measurement and Test Methods	406
● Potentiometers Resistance Taper	408

Note

- indicates applicability to all products in the series.

Insulated Shaft Potentiometers Soldering Conditions

■ Reference for Hand Soldering

Series	Tip temperature	Soldering time	No. of solders
RK09D, RK09K, RK09Y11L, RK11K, RK12L, RK12L115, RK14K	350°C max.	3s max.	1 time

■ Reference for Dip Soldering

Series	Preheating		Dip soldering		No. of solders
	Soldering surface temperature	Heating time	Soldering temperature	Soldering time	
RK12L	100°C	1 min. max.	260°C max.	5s max.	2 time max.

Rotary
Potentiometers

Slide
Potentiometers

Metal
Shaft

Insulated
Shaft

Knob
Operating

Ring Type