

- Interface Materials**
- Insulators
 - Aluminum Oxide Ceramic
 - Insulating Covers
 - Bushings
 - Mica
 - Thermasil
 - Beryllium Oxide Ceramic
 - Hard Anodized Aluminum

Beryllium Oxide Ceramic

Check Distributor Stock
Enter a part number for pricing and availability.

RoHS Compliant

[MSDS Safety Sheet for Beryllium Oxide Ceramic in PDF format](#)


Beryllium oxide insulators have a high dielectric strength, which allows safe operating voltages of 1500 volts or more. For applications involving high frequency or high pulse rate circuitry, the inherent low electrical capacitance of these insulators prevents circuit detuning and loss of signal power.

Beryllium oxide insulators have a dielectric strength of approximately 22.8 x 10³ volts/mm for .81mm material (580 volts/mil for .032" material), and 17.7 x 10³ volts/mm for 1.57mm material (450 volts/mil for .062 material). The thermal conductivity of beryllium oxide is 221.94 Wm⁻¹ °C⁻¹ (128.2 Btu/hr.ft. °F).

Beryllium oxide is chemically inert and completely safe to use in its fired state. Handling of finished parts presents absolutely no health hazards.

Beryllium oxide, however, is toxic when dust, mist or fumes containing particles small enough to enter the lungs are inhaled. Therefore, grindings, sanding, and pulverizing the material should be avoided.

For TO-3




- "A" = 39.65 (1.561)
- "B" = 26.67 (1.050)
- "C" = 3.68 (0.145)
- "D" = 3.68 (0.145)

Part No. 4003G Thickness 0.062 (1.57) [Download PCN](#)


Part No. 4003-1 Thickness 0.032 (0.81)

For TO-5 and TO-18



Part No.	A	B	C	Thickness
4005G (TO-5)	9.14 (0.360)	5.08 (0.200)	1.02 (0.040)	0.76 (0.030)
4005-15 (TO-5)	9.14 (0.360)	5.08 (0.200)	1.02 (0.040)	0.38 (0.015)
4018G (TO-18)	5.59 (0.220)	2.54 (0.100)	1.02 (0.040)	0.76 (0.030)

Mounting Washers



Part No.	OD	ID	Thickness
B-250-130-62G	6.95±0.13 (0.250 ±0.005)	3.30±0.13 (0.130 ±0.005)	1.57±0.25 (0.062 ±0.010)
B-470-235-40G	11.94±0.13 (0.470 ±0.005)	5.97±0.13 (0.235 ±0.005)	1.02±0.13 (0.040 ±0.005)
B-510-200-40G	12.95±0.25 (0.510 ±0.010)	5.08±0.25 (0.200 ±0.010)	1.02±0.13 (0.040 ±0.005)
B-800-260-30G	20.32±0.25 (0.800 ±0.010)	8.80±0.13 (0.280 ±0.005)	.78±0.08 (0.030 ±0.003)
B-800-260-62G	20.32±0.25 (0.800 ±0.010)	6.60±0.13 (0.260 ±0.005)	1.57±0.25 (0.062 ±0.010)

Beryllium Oxide

PROPERTY	TYPICAL VALUE 25°C	TEST METHOD
CHEMICAL		
BeO content	99.5% minimum	Spectograph Analysis (100%-% by wt. of total metallic impurity).
ELECTRICAL		
Dielectric Constant 25°C (77°F)	6.5 (1MHz) 6.6 (10GHz)	ASTM D150-70 ASTM D2520-70
Dissipation Factor 25°C (77°F)	.0004 (1MHz) .0004 (10GHz)	ASTM D150 ASTM D2520

Electrical Resistivity 25°C (77°F)	>1015 ohm-cm	ASTM D150 ASTM D257-61
Dielectric Strength (AC)	22.8 x 103 volts/mm (.81mm) [580 volts/mil (0.32")]	ASTM D149-84
PHYSICAL		
Density	2.85 g/cm ³ (min) 177.93 Lb/ft ³	ASTM C373-66 ASTM F77-671
Hardness	60 minimum (Rockwel 45N)	ASTM E18-67
MECHANICAL		
Flexural Strength 25°C (77°F)	2.27 x 108Pa (min.) (33,000 psi min.)	ASTM Microbar 8025 ASTM D2442-70A3
Modules of Elasticity	3.45 x 1011Pa (50 x 106psi)	ASTM D2442-70A4
Poisson's Ratio	0.26	ASTM D2442-70A4
Tensile Strength 25°C (77°F)	1.52 x 108Pa (22,000 psi)	ASTM 565-66T
Compressive Strength 25°C (77°F)	1.55 x 109 Pa (25,000 psi)	ASTM C528
THERMAL		
Coefficient of Thermal Expansion	9.0 x 10-6 /°C 5.0 x 10-6 /°F	ASTM E-228 ASTM C372-56 ASTM C327-56 ASTM C408-82
Thermal Conductivity	251.28 Wm-1°C-1(25°F) [145.14 Btu/hr.ft °F] (77°F) 186.44 Wm-1°C-1(100°F) [106.86 Btu/hr.ft °F] (212°F) 146.57 Wm-1°C-1(150°F) [84.67 Btu/hr.ft °F] (302°F)	ASTM C408-82
Specific Heat (180°C)	1.0 x 10-3 KJ/Kg°C [2.5 x 10-4 Btu/Lb °F]	ASTM C351-81
Melting Point	2552°C (4625°F)	
Maximum Temperature for Continuous Use	2149°C (3900°F)	

Customer Assistance

- Contact Us
- Get Design Assistance
- Find a Distributor
- Find a Sales Rep
- Request a Quote
- Placing an Order
- Terms and Conditions
- Returns

Popular Products

- Fans
- Extrusions
- Board Level
- Liquid Cooling
- Heat Pipe Technology
- Heat Sink Accessories
- Interface Materials

Our Company

- News and Events
- Management Team
- Worldwide Locations
- Directions to Headquarters
- Disclaimer
- Customer Survey
- Privacy Policy

Connect with Aavid

Sign up for Aavid News & Alerts

Email Address

Like / Follow / Connect



© Copyright 2015 Aavid Thermalloy, LLC.