

## Rail Mounted Clips

The Maxclip System  
Find a Clip

- » [Find a Sales Associate](#)
- » [Find a Distributor](#)
- » [Design Assistance](#)

### Check Distributor Stock

Enter a part number for pricing and availability.

### Application Info

[Installation Demo Video](#)

[Thermal Performance](#)

[Tabless Packages](#)

[Tin Plated Pins](#)

















[Shock and Vibration Testing](#)

[Choosing a Clip](#)

[Interface material selection](#)

Please note that these clips are intended solely for use with Aavid Thermalloy **Max Clip Extrusion Profiles**.

<p><b>Part Number: MAX01NG</b> Low force clip</p> <p><b>RoHS Compliant</b></p> <p></p> <p><b>Force:</b> 22 N [4.9 lbs] <b>Width:</b> 10 mm [0.39 in] <b>Thickness:</b> 0.5 mm [0.02 in]</p>	
<p><b>Part Number: MAX01-HNG</b> High force clip</p> <p><b>RoHS Compliant</b></p> <p></p> <p><b>Force:</b> 80 N [18.0 lbs] <b>Width:</b> 10 mm [0.39 in] <b>Thickness:</b> 0.7 mm [0.03 in]</p>	
<p><b>Part Number: MAX02NG</b> Standard force clip</p> <p><b>RoHS Compliant</b></p> <p></p> <p><b>Force:</b> 35 N [7.9 lbs] <b>Width:</b> 12 mm [0.47 in] <b>Thickness:</b> 0.5 mm [0.02 in]</p>	
<p><b>Part Number: MAX02-HNG</b> High force clip</p> <p><b>RoHS Compliant</b></p> <p></p> <p><b>Force:</b> 60 N [13.5 lbs] <b>Width:</b> 13 mm [0.51 in] <b>Thickness:</b> 0.6 mm [0.02 in]</p>	
<p><b>Part Number: MAX03NG</b> Standard force clip</p> <p><b>RoHS Compliant</b></p> <p></p> <p><b>Force:</b> 45 N [10.1 lbs] <b>Width:</b> 15 mm [0.59 in] <b>Thickness:</b> 0.5 mm [0.02 in]</p>	
<p><b>Part Number: MAX03-HNG</b> High force clip</p> <p><b>RoHS Compliant</b></p> <p></p> <p><b>Force:</b> 80 N [18.0 lbs] <b>Width:</b> 18 mm [0.71 in] <b>Thickness:</b> 0.6 mm [0.02 in]</p>	
<p><b>Part Number: MAX04NG</b> Standard force clip</p> <p><b>RoHS Compliant</b></p> <p></p> <p><b>Force:</b> 60 N [13.5 lbs] <b>Width:</b> 20 mm [0.79 in] <b>Thickness:</b> 0.5 mm [0.02 in]</p>	
<p><b>Part Number: MAX09NG</b> Short standard force clip</p> <p><b>RoHS Compliant</b></p> <p><b>Force:</b> 45 N [10.1 lbs] <b>Width:</b> 10 mm [0.39 in] <b>Thickness:</b> 0.5 mm [0.02 in]</p>	
<p><b>Part Number: MAX10NG</b> Long standard force clip</p> <p><b>RoHS Compliant</b></p> <p></p> <p><b>Force:</b> 40 N [9.0 lbs] <b>Width:</b> 12 mm [0.47 in] <b>Thickness:</b> 0.6 mm [0.02 in]</p>	

<b>Part Number: MAX12NG</b> Low force clip RoHS  Compliant 	 T092 Sensors 19.7 [0.78]
<b>Force:</b> 25 N [5.6 lbs] <b>Width:</b> 6 mm [0.24 in] <b>Thickness:</b> 0.6 mm [0.02 in]	
<b>Part Number: MAX11NG</b> Extra long standard force clip RoHS  Compliant 	 T0220/Max220 Thin components 24.7 [0.97]
<b>Force:</b> 40 N [9.0 lbs] <b>Width:</b> 12 mm [0.47 in] <b>Thickness:</b> 0.6 mm [0.02 in]	
<b>Part Number: MAX23NG</b> High force clip for use with thick insulator RoHS  Compliant	 T0247/Max247 4.0 [0.16] T0247J INSULATOR
<b>Force:</b> 100 N [22.5 lbs] <b>Width:</b> 18 mm [0.71 in] <b>Thickness:</b> 0.6 mm [0.02 in]	
<b>Part Number: MAX20NG</b> Standard force clip for use with thick insulator RoHS  Compliant	 T0220/Max220 4.0 [0.16] INSULATOR
<b>Force:</b> 47 N [10.6 lbs] <b>Width:</b> 12 mm [0.47 in] <b>Thickness:</b> 0.6 mm [0.02 in]	
<b>Part Number: MAX13NG</b> Standard force clip with locating features RoHS  Compliant	 T0247 10.5 [0.41]
<b>Force:</b> 45 N [10.1 lbs] <b>Width:</b> 17 mm [0.67 in] <b>Thickness:</b> 0.5 mm [0.02 in]	
<b>Part Number: MAX14NG</b> Low force clip with locating features RoHS  Compliant	 T0220 14.5 [0.57]
<b>Force:</b> 20 N [4.5 lbs] <b>Width:</b> 13 mm [0.51 in] <b>Thickness:</b> 0.5 mm [0.02 in]	
<b>Part Number: MAX16NG</b> Standard force clip with locating features RoHS  Compliant	 T0247 10.5 [0.41]
<b>Force:</b> 45 N [10.1 lbs] <b>Width:</b> 17 mm [0.67 in] <b>Thickness:</b> 0.5 mm [0.02 in]	

## Customer Assistance

- [Contact Us](#)
- [Get Design Assistance](#)
- [Find a Distributor](#)
- [Find a Sales Rep](#)
- [Request a Quote](#)
- [Placing an Order](#)
- [Terms and Conditions](#)
- [Returns](#)

## Popular Products

- [Fans](#)
- [Extrusions](#)
- [Board Level](#)
- [Liquid Cooling](#)
- [Heat Pipe Technology](#)
- [Heat Sink Accessories](#)
- [Interface Materials](#)

## Our Company

- [News and Events](#)
- [Management Team](#)
- [Worldwide Locations](#)
- [Directions to Headquarters](#)
- [Disclaimer](#)
- [Customer Survey](#)
- [Privacy Policy](#)

## Connect with Aavid

Sign up for Aavid News & Alerts

Email Address

Like / Follow / Connect



© Copyright 2015 Aavid Thermalloy, LLC.