

Products → Low Voltage Products and Systems → Control Products → Signal Converters
→ Analog Signal Converters

General Information

Extended Product Type:	CC-E V/I
Product ID:	1SVR011721R1000
EAN:	4013614351617
Catalog Description:	CC-E V/I Signal converter, singlef. 0-10V / 0-20mA, 110-240VAC
Long Description:	The CC-E V/I is a single-function standard analog signal converter from the CC-E range. This converter, with 3-way electrical isolation, operates with a rated control supply voltage of 110-240 V AC. It provides an input signal range of 0-10 V and an output signal range of 0-20 mA. Applied supply voltage is displayed by a green LED.

Ordering

EAN:	4013614351617
Minimum Order Quantity:	1 piece
Customs Tariff Number:	85369095

Container Information

Package Level 1 Units:	1 piece
Package Level 1 Width:	81 mm
Package Level 1 Length:	27 mm
Package Level 1 Height:	109 mm
Package Level 1 Gross Weight:	0.101 kg
Package Level 1 EAN:	4013614351617

Dimensions

Product Net Width:	22.5 mm
Product Net Height:	75 mm
Product Net Depth:	107 mm
Product Net Weight:	0.087 kg

Technical

Function:	Standard signals Single-function
Input Signal:	0 ... 10 V
Output Signal:	0 ... 20 mA
Rated Control Supply Voltage (U_s):	110 ... 240 V AC

Environmental

RoHS Status:

Following EU Directive 2011/65/EU

Certificates and Declarations (Document Number)

cUL Certificate:	cUL508_E174460
Data Sheet, Technical Information:	2CDC110004C0210
Declaration of Conformity - CE:	1SVD981003-0001
Environmental Information:	1SAA981006-2402
Instructions and Manuals:	1SVC011700M9000
RoHS Information:	1SVD981003-0001
UL Certificate:	UL508_E174460

Classifications

Object Classification Code:	T
ETIM 4:	EC002653 - Isolation amplifier
ETIM 5:	EC002653 - Isolation amplifier
ETIM 6:	EC002653 - Isolation amplifier
ETIM 7:	EC002653 - Isolation amplifier
eClass:	7.0 27210120
UNSPSC:	39120000

