


You can view this page in:

- EN
- DE
- SV
- FR
- C6
- DA
- EL
- ES
- FR
- HU
- IT
- JA
- KO
- NL
- NO
- PL
- PT
- RU
- SK
- TR
- ZH

# Detailed information for: TA80DU-63

This page contains technical data sheet, documents library and links to offering related to this product. If you require any other information, please contact us using form located at the bottom of the page.

 [Print...](#)

 [Print to Pdf...](#)

[Data Sheet](#)

[Downloads](#)

## TA80DU-63

### General Information




**Extended Product Type:** TA80DU-63

**Product ID:** 1SAZ331201R1005

**EAN:** 4013614216770

**Catalog Description:** TA80DU-63 Thermal Overload Relay

**Long Description:** The TA80DU-63 thermal overload relay is an economic electromechanical protection device for the main circuit. It offers reliable and fast protection for motors in the event of overload or phase failure. The device has trip class 10A. Further features are the temperature compensation, trip contact (NC), signal contact (NO), automatic- or manual reset selectable, trip-free mechanism, STOP- and Test function and a trip indication. The overload relays are connected directly to the block contactors. Single mounting kits are available as accessory.



### Categories

Products » Low Voltage Products and Systems » Control Products » Contactors » Thermal Overload Relays

### Ordering

**Minimum Order Quantity:** 1 piece

**Customs Tariff Number:** 85364900

### Popular Downloads

**Data Sheet, Technical Information:** [1SBC100173C0201](#)

**Data Sheet, Technical Information:** [1SAZ300501F0003](#)

**Information (Part 2):****Instructions and Manuals:** [2CDC106080M6802](#)**Dimension Diagram:** [1SAZ300403F0001](#)**Dimensions****Product Net Width:** 78 mm**Product Net Height:** 97 mm**Product Net Depth / Length:** 111 mm**Product Net Weight:** 0.365 kg**Technical****Setting Range:** 45 ... 63 A**Rated Operational Voltage:** Auxiliary Circuit 440 V DC  
Auxiliary Circuit 500 V AC  
Main Circuit 690 V AC**Rated Operational Current ( $I_e$ ):** 63 A**Rated Operational Current AC-3 ( $I_e$ ):** 63 A**Rated Frequency (f):** Auxiliary Circuit 50 Hz  
Auxiliary Circuit 60 Hz  
Auxiliary Circuit DC  
Main Circuit 60 Hz  
Main Circuit 50 Hz  
Main Circuit DC**Rated Impulse Withstand Voltage ( $U_{imp}$ ):** Auxiliary Circuit 6 kV  
Main Circuit 6 kV**Rated Insulation Voltage ( $U_i$ ):** 690 V**Number of Poles:** 3**Number of Auxiliary Contacts NC:** 1**Number of Auxiliary Contacts NO:** 1**Number of Protected Poles:** 3**Conventional Free-air Thermal Current ( $I_{th}$ ):** Auxiliary Circuit NC 5 A  
Auxiliary Circuit NO 5 A**Rated Operational Current AC-15 ( $I_e$ ):** (120 V) NC 3 A  
(120 V) NO 1.5 A  
(240 V) NC 3 A  
(240 V) NO 1.5 A  
(400 V) NC 1.9 A  
(400 V) NO 1 A  
(440 V) NC 1 A  
(440 V) NO 1 A  
(500 V) NC 1 A  
(500 V) NO 1 A**Rated Operational Current DC-13 ( $I_e$ ):** (125 V) NC 0.25 A  
(125 V) NO 0.25 A  
(24 V) NC 1.25 A  
(24 V) NO 1.25 A  
(250 V) NC 0.12 A  
(250 V) NO 0.04 A  
(60 V) NC 0.25 A  
(60 V) NO 0.25 A**Degree of Protection:** Housing IP20  
Main Circuit Terminals IP10**Pollution Degree:** 3

<b>Connecting Capacity Auxiliary Circuit:</b>	Flexible with Ferrule 1/2x 0.75 ... 2.5 mm <sup>2</sup> Flexible 1/2x 0.75 ... 2.5 mm <sup>2</sup> Rigid 1/2x 0.75 ... 4 mm <sup>2</sup>
<b>Connecting Capacity Main Circuit:</b>	Flexible with Ferrule 1x 2.5 ... 25 mm <sup>2</sup> Flexible with Ferrule 2x 2.5 ... 10 mm <sup>2</sup> Rigid 1x 2.5 ... 25 mm <sup>2</sup> Rigid 2x 2.5 ... 16 mm <sup>2</sup>
<b>Tightening Torque:</b>	Auxiliary Circuit 1 ... 1.3 N·m Main Circuit 4.5 N·m
<b>Wire Stripping Length:</b>	Auxiliary Circuit 9 mm Main Circuit 14 mm
<b>Recommended Screw Driver:</b>	Auxiliary Circuit Pozidriv 1 Main Circuit Pozidriv 2
<b>Power Loss:</b>	at Rated Operating Conditions per Pole 1.9 W
<b>Suitable For:</b>	A95 A110 AE95 AE110
<b>Standards:</b>	IEC/EN 60947-1 IEC/EN 60947-4-1 IEC/EN 60947-5-1 UL 60947-1 UL 60947-4-1

#### Technical UL/CSA

<b>Maximum Operating Voltage UL/CSA:</b>	Main Circuit 600 V AC
<b>Ampere Rating UL/CSA:</b>	63 A
<b>Contact Rating UL/CSA:</b>	(NC:) B600 (NO:) C600
<b>Connecting Capacity Main Circuit UL/CSA:</b>	Flexible 1/2x 8-1 AWG Stranded 1/2x 8-1 AWG
<b>Connecting Capacity Auxiliary Circuit UL/CSA:</b>	Flexible 1/2x 18-14 AWG Stranded 1/2x 18-14 AWG
<b>Tightening Torque UL/CSA:</b>	Auxiliary Circuit 12 in·lb Main Circuit 40 in·lb

#### Environmental

<b>Ambient Air Temperature:</b>	Operation -25 ... +55 °C Operation Compensated -25 ... +55 °C Storage -40 ... +70 °C
<b>Ambient Air Temperature Compensation:</b>	Yes
<b>Maximum Operating Altitude Permissible:</b>	2000 m
<b>Resistance to Shock acc. to IEC 60068-2-27:</b>	11 ms Pulse 12g
<b>RoHS Status:</b>	Following EU Directive 2011/65/EU

#### Certificates and Declarations (Document Number)

<b>ABS Certificate:</b>	<a href="#"><u>1SAA941000-0102</u></a>
<b>BV Certificate:</b>	<a href="#"><u>1SAA941000-0201</u></a>
<b>CB Certificate:</b>	<a href="#"><u>1SAA941017-2001</u></a>
<b>CQC Certificate:</b>	<a href="#"><u>CQC2016010309922938</u></a>

<b>cUL Certificate:</b>	<a href="#">cUL_E48139</a>
<b>Declaration of Conformity - CCC:</b>	<a href="#">2020980304001323</a>
<b>Declaration of Conformity - CE:</b>	<a href="#">1SAD938517-0043</a>
<b>DNV Certificate:</b>	<a href="#">1SAA941000-0304</a>
<b>DNV GL Certificate:</b>	<a href="#">1SAA941000-0304</a>
<b>EAC Certificate:</b>	<a href="#">1SAA941002-2702</a>
<b>GL Certificate:</b>	<a href="#">1SAA941000-0304</a>
<b>GOST Certificate:</b>	<a href="#">1SAA941000-2704</a>
<b>Instructions and Manuals:</b>	<a href="#">2CDC106080M6802</a>
<b>LR Certificate:</b>	<a href="#">1SAA941000-0504</a>
<b>RMRS Certificate:</b>	<a href="#">1SAA941000-0704</a>
<b>RoHS Information:</b>	<a href="#">1SAD938514-0043</a>
<b>UL Certificate:</b>	<a href="#">UL_E48139</a> <a href="#">1SAA938001-1604</a>

### Container Information

<b>Package Level 1 Units:</b>	1 piece
<b>Package Level 1 Width:</b>	105 mm
<b>Package Level 1 Height:</b>	90 mm
<b>Package Level 1 Depth / Length:</b>	125 mm
<b>Package Level 1 Gross Weight:</b>	0.405 kg
<b>Package Level 1 EAN:</b>	4013614216770
<b>Package Level 2 Units:</b>	16 piece
<b>Package Level 2 Width:</b>	280 mm
<b>Package Level 2 Height:</b>	210 mm
<b>Package Level 2 Depth / Length:</b>	395 mm
<b>Package Level 2 Gross Weight:</b>	8.786 kg
<b>Package Level 2 EAN:</b>	4013614494024

### Classifications

<b>Object Classification Code:</b>	F
<b>ETIM 4:</b>	EC000106 - Thermal overload relay
<b>ETIM 5:</b>	EC000106 - Thermal overload relay
<b>ETIM 6:</b>	EC000106 - Thermal overload relay
<b>ETIM 7:</b>	EC000106 - Thermal overload relay
<b>eClass:</b>	V11.0 : 27371501
<b>UNSPSC:</b>	39121520
<b>IDEA Granular Category Code (IGCC):</b>	5364 >> Overload relay
<b>E-Number (Finland):</b>	3709353



## Contact us

Submit your inquiry and we will contact you

[CONTACT US](#)

Or contact your [ABB Contact Center](#)