

# Detailed information for: VE5-2

This page contains technical data sheet, documents library and links to offering related to this product. If you require any other information, please contact us using form located at the bottom of the page.

[Print...](#)

[Print to Pdf...](#)

Data Sheet

Documentation

## VE5-2

### General Information

Extended Product Type:VE5-2

Product ID:	1SBN030210R1000
EAN:	3471522121387
Catalog Description:	VE5-2 Block Contactor Accessories
Long Description:	VE5-2 Block Contactor Accessories

### Categories

Products » Low Voltage Products and Systems » Control Products » Contactors » Block Contactors Accessories



### Ordering

EAN:	3471522121387
Minimum Order Quantity:	1 piece
Customs Tariff Number:	85389099

### Dimensions

Product Net Weight:	0.146 kg
---------------------	----------

### Container Information

Package Level 1 Units:	1 piece
Package Level 1 Gross Weight:	0.146 kg

Package Level 1 EAN: 3471522121387

Package Level 2 Units: 36 piece

## Environmental

RoHS Status: Following EU Directive 2002/95/EC August 18, 2005 and amendment

## Additional Information

Conventional Free-air Thermal Current ( $I_{th}$ ): acc. to IEC 60947-5-1,  $q = 40\text{ °C}$  16.0 A

IIT Publishing Status: Level 0 - Information enabled

Mechanical Durability: 5 million

Mounted Auxiliary Contacts: 0 NO, 2 NC

Mounting on Contactors: A 45...A 110

Mounting Type: rail or plate not supplied (The combination of A 45 ... A 75 interlocked with A 95, A 110 cannot be mounted on symmetrical rail - 75 mm EN 50023)

Number of Auxiliary Contacts NC: 2

Order Multiple: 1 piece

Power Loss: at Rated Operating Conditions per Pole 0.1 W

Product Main Type: Accessories for Block Contactors

Product Name: Block Contactor Accessories

Rated Breaking Capacity acc. to IEC 60947-5-1: 10 x  $I_e$  AC-15

Rated Frequency (f): Supply Circuit 50 Hz  
Supply Circuit 60 Hz

Rated Insulation Voltage ( $U_i$ ): acc. to IEC 60947-5-1 and VDE 0110 (Gr. C) 690 V  
acc. to UL/CSA 600 V

Rated Making Capacity acc. to IEC 60947-5-1: 10 x  $I_e$  AC-15

Rated Operational Current AC-15 ( $I_e$ ): (220 / 240 V) 4 A  
(24 / 127 V) 6 A  
(380 / 440 V) 3 A  
(500 V) 2 A  
(690 V) 2 A

Rated Operational Current DC-13 ( $I_e$ ): (125 V) 0.55 A  
(24 V) 6 A  
(250 V) 0.3 A  
(48 V) 2.8 A  
(72 V) 1 A

Rated Operational Voltage: Auxiliary Circuit 690 V

Rated Short-time Withstand Current ( $I_{cw}$ ): for 0.1 s 140.0 A  
for 1 s 100 A

Suitable For: AX50  
AX65  
AX80  
AX95  
AX115  
AX150

Terminal Type: Screw Terminals

Version: Mechanical/Electrical

## Certificates and Declarations (Document Number)

CB Certificate: [CB\\_CN\\_37804](#)

CCC Certificate: [CCC\\_2016010304881659](#)


Declaration of Conformity - CE:	1SBD250814U1000
Environmental Information:	1SBD250146E1000
GOST Certificate:	GOST_POCCFRME77B07175
Instructions and Manuals:	FPTC407713P0002
RINA Certificate:	RINA_ELE128713XG001
RoHS Information:	1SBC101061D0201
Data Sheet, Technical Information:	1SBC100122C0202_Ch04

## Classifications

E-nummer:	3228827
ETIM 4:	EC002498 - Accessories for low-voltage switch technology
ETIM 5:	EC002498 - Accessories for low-voltage switch technology
ETIM 6:	EC002498 - Accessories for low-voltage switch technology
UNSPSC:	39120000

## Contact information

What would you like to do?



### Submit your inquiry

Country

United States of America ▼

Name

Company

E-Mail

Phone

Zip code

Your message

[→ Privacy policy](#)

Cancel

[Send message](#)

### Your local ABB Sales Team

Name

Customer Support

[▲ Close](#)