



General Purpose

- Energy Efficient Single-Phase Transformers
- Energy Efficient Three-Phase Transformers
- Non-linear Load Transformers
- Harmonic Mitigating Transformers
- Power wise C3 Transformers

Industrial Control Transformers

- Open Core and Coil (TA and TB)
- Encapsulated (AE and CE)
- Finger Safe
- Harsh Environment

Appliance Transformers

Drive Isolation Transformers

Line Reactors

Low Voltage/Lighting Transformers

Buck Boost Transformers

Power Supplies

- Regulated Linear
- Unregulated Linear

Panel Tran

Power Conditioning



Regulated Linear Power Supplies

The "SPS BlueLine" series provides 15 to 120 watts of DC power with adjustable output voltages and selectable inputs of 115/230V AC, 47-440Hz. Floating outputs on most models and optional OVP on most models for greater versatility.

The "SPW" series regulated linear power supplies are accepted world-wide for selectable AC input voltages of 100 through 240V and meet UL, CSA and TUV standards. These units have overload protection with automatic recover and 100% burn-in. All 5V output models have built-in voltage protection.

SPS BlueLine Series 2.0 to 144 Watts of DC Power

Catalog No.	H	Dimensions			Ship Weight	Input Volts	Output VDC	Output Amps
		W	L					
SFS-3012	4.75 (12.1)	4.00 (10.2)	2.50 (6.35)	3.3 (1.5)	120/(240)	12	1.8	
SPS-6012	5.02 (12.7)	6.00 (15.2)	4.94 (12.5)	7.1 (3.2)	120/(240)	12	5.0	
SPS-152428	2.39 (6.1)	4.00 (10.2)	4.50 (11.4)	2.14 (1.3)	120	24/28	0.8/0.6	
SPS-302428	4.75 (12.1)	4.00 (10.2)	2.50 (6.35)	3.3 (1.5)	120/(240)	24/28	1.2/1.0	

SPW Series 15 Watts to 175 Watts

Input Voltage: 100/120/220/230/240 Selectable

Catalog No.	H	Dimensions			Ship Weight	Output VDC	Output Amps	Case
		W	L					
SPWS-53-OV	1.62 (4.1)	4.84 (12.3)	3.99 (10.1)	2.43 (1.1)	5	3.0	A	
SPWS-2424	2.50 (6.3)	4.87 (12.4)	5.62 (14.3)	4 (1.8)	24	2.4	B	
SPWS-2436	2.75 (7.0)	7.00 (17.8)	4.87 (12.4)	7.28 (3.3)	24	3.6	C	
SPWS-2472	2.75 (7.0)	14.00 (35.6)	4.87 (12.4)	8.82 (4.0)	24	7.2	E	