

SOLID AND 26-28 STRANDED CONNECTOR WIRES.

- 2) DIELECTRIC: PBT GLASS FIBER RE-INFORCED, UL-94V0
- 3) CONTACT MATERIIAL: COPPER ALLOY
- 4) CONTACT: 20 MICRO-INCHES MIN. GOLD MATING AREA: 3-5 MICRO-INCHES GOLD TERMINAL AREA: 50 MICRO-INCHES MIN. NICKEL UNDERPLATING ALL OVER.
- 5) SHELL MATERIAL: ZINC PLATED STEEL WITH CLEAR CHROMATE COATING
- 6) CURRENT CAPACITY: 5 AMPS/CONTACT
- 7) VOLTAGE RATING: 700 VOLTS D.C. AT SEA LEVEL 200 VOLTS D.C. AT 70,000 FEET
- 8) INSULATION RESISTANCE: >5000 M OHM
- 9) DIELECTRIC WITHSTANDING VOLTAGE: 1200 VAC (RMS) AT SEA LEVEL
- 10) CONNECTOR MATING FORCE: REFER TO TABLE 1.
- 11) CONTACT RETENTION FORCE: 2 LBS MAX.
- 12) DURABILITY: 250 CYCLES MIN.
- 13) VIBRATION: NO INTERRUPTIONS < 1u SEC.
- 14) OPERATING TEMPERATURE: -55° C TO $+105^{\circ}$ C $(-67^{\circ}$ F TO $+221^{\circ}$ F)

TABLE 1

ECN

A HK

CONNECTOR SIZES	AVERAGE MATING FORCE (POUNDS)				
14	5				
24	8				
36	12				
50	15				
$6\overline{4}$	19				

REVISIONS

APPROVED

Y.M.LEE

DATE

3/26/01

DESCRIPTION

INITIAL RELEASE

CUSTOMER INFORMATION DRAWING

ITEM NO		PART OR TIFICATION NO			NOMENCLATURE OR DESCRIPTION			OTY REQ'D			
	PARTS LIST										
UNLESS OTHERWISE SPECIFIED TOLERANCES		APP	APPROVAL DATE		Amphenol						
	U.S. METRIC		DRAWN	Y.M. LEE	03/26/01	<i>F</i>					
.x +	.XX +/- 0.010 .XXX +/- 0.005 FRACTIONS +/-		CHECKED	Y.M. LEE	03/26/01	Amphenol East As					
-XX +			CHECKED			Manufacturing Operation					
FRACTIO						TITLE 50 CONTACT PLUG ASSEM				Y	
ANGLES +/- 1'		DRAWING FILE :			RUNNING CABLE 1-26 END 28 & 26 AWG WIRE, DUST COVE						
FOR MATERIALS AND FINISHES SEE NOTES		\DRAWING\157\C157725003.DWG									
REMOVE SHARP EDGES		ANGLE	ANGLE OF PROJECTION		SIZE DRAWING NO.				REV.		
DIMENSIONS											
U	.s.	INCHES	1 (())	_ —	A3	U-3	A			
-(MET	RIC)	-(MM)-		Ψ \subseteq		SCA	ALE	NONE	SHEET 1	OF 1	
2		•	•					1			