

SCERX22ACA Product Details



SCERX22ACA

 [Active](#)

Time Delay Relays

[Not EU RoHS or ELV Compliant](#)

Product Highlights:

- ? SCE Specification Grade True Off - Delay Timing Series
- ? Time Delay Relay
- ? Input Voltage = 120 VAC
- ? Input Voltage = 125 VDC
- ? Contact Arrangement = 2 Form C, DPDT, 2 C/O

[View all Features](#) | [Find Similar Products](#)

Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling Product Feature Selector](#)
- [Contact Us About This Product](#)

Documentation & Additional Information

Product Drawings:

- ? None Available

Catalog Pages/Data Sheets:

- ? None Available

Product Specifications:

- ? None Available

Application Specifications:

- ? None Available

Instruction Sheets:

- ? None Available

CAD Files:

- ? None Available

Additional Information:

- ? [Product Line Information](#)

Related Products:

- ? [Tooling](#)

Product Features

(Please use the Product Drawing for all design activity)

Product Type Features:

- ? Product Type = Time Delay Relay
- ? Termination Type = 8 -Pin Octal Style Plug

Electrical Characteristics:

- ? Input Voltage (VAC) = 120
- ? Input Voltage (VDC) = 125
- ? Contact Rating = 5A Resistive @ 120/240 VAC

Body Related Features:

- ? [Series](#) = SCE Specification Grade True Off - Delay Timing

Contact Related Features:

- ? Mounting Options = Socket
- ? Mode of Operation = True Off -Delay
- ? Delay Time = 1 second to 30 seconds
- ? Type of Control = Knob
- ? Repeatability, Max. = $\pm 1\%$
- ? Approved Standards = CE Approved, CSA Certified, UL Recognized
- ? Approx. Dimensions (L x W x H) (mm [in]) = 50.00 x 50.00 x 83.00 [1.970 x 1.970 x 3.270]

Configuration Related Features:

- ? [Contact Arrangement](#) = 2 Form C, DPDT, 2 C/O
- ? Multiple Timing Ranges = Without

Industry Standards:

- ? [RoHS/ELV Compliance](#) = Not ELV/RoHS compliant
- ? [Lead Free Solder Processes](#) = Not suitable for lead free processing

Conditions for Usage:

- ? Temperature Range (°C) = -30 - +65

Other:

- ? Brand = Agastat