


Product Details for 1 -1337604 -0



1 -1337604 -0

[Active](#)

SMB RF Connectors

[RoHS Compliant](#) (Statement of Compliance)

Product Highlights:

- ? Connector
- ? Jack Receptacle
- ? Standard
- ? Terminate To Printed Circuit Board
- ? Coupler Style = Snap -On

[View all Features](#)

Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

Documentation & Additional Information

Product Drawings:

- ? [SMB SURFACE MOUNT STRAIGHT PCB SOCKET 50 OHM](#) (PDF, English)

Catalog Pages/Data Sheets:

- ? None Available

Product Specifications:

- ? None Available

Application Specifications:

- ? None Available

Instruction Sheets:

- ? None Available

CAD Files:

- ? None Available

Additional Information:

- ? [Product Line Information](#)

Related Products:

- ? [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- ? [Product Type](#) = Connector
- ? Gender = Jack Receptacle
- ? Connector Series = Standard
- ? [Body Style](#) = Straight
- ? [Grade](#) = Professional
- ? [PCB Mount Angle](#) = Vertical
- ? Board Standoff = Without
- ? PCB Mount Style = Surface Mount
- ? Body Material = Brass
- ? Dielectric Material = PTFE
- ? Sealed = No
- ? Isolated = No
- ? Body Shape = Square
- ? PCB Height (mm [in]) = 7.70 [0.303]

Mechanical Attachment:

- ? [Panel Attachment](#) = Without
- ? Flange Dimension [Sq.] (mm [in]) = 6.35 [0.250]

Electrical Characteristics:

- ? [Connector Impedance \(?\)](#) = 50
- ? Environmental Seal = Without

Body Related Features:

- ? Coupler Style = Snap -On
- ? [Pin Protection](#) = Without
- ? Solder Lug = Without
- ? [Body Plating](#) = Gold
- ? Overall Length (mm [in]) = 7.70 [0.303]
- ? Polarized = No

Contact Related Features:

- ? [Center Contact Plating](#) = Gold
- ? Contacts = With
- ? Center Contact Material = Brass

Industry Standards:

- ? [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- ? [Lead Free Solder Processes](#) = Reflow solder capable to 245°C, Reflow solder capable to 260°C
- ? RoHS/ELV Compliance History = Converted to comply with RoHS directive

Conditions for Usage:

- ? [Terminate To](#) = Printed Circuit Board
- ? Operating Temperature (Max.) (°C) = 165

Packaging Related Features:

- ? Packaging Quantity = 100
- ? Packaging Method = Individual

Other:

- ? Brand = Greenpar