




△ 1-1478601-1


TE LOGO AND PART NUMBER MARKED IN THIS AREA



SPECIFICATIONS	
Rating	6A 125/250V AC
Contact Resistance	50 mΩ max.
Insulation Resistance	100 MΩ min. DC500V
Dielectric Strength	1000V AC 1 minute
Mechanical Life	1,000,000 cycles
Electrical Life	50,000 cycles @6A 250V, resistive load
Operating Temperature Range	-40°C to +125°C RH 85% max.
Soldering Temperature	260 ± 5°C 3sec



Hole Pattern for PCB



△ VDE/ENEC APPROVAL IN PROGRESS

- NOTES:
- FOR TECHNICAL DATA REFER TO YOUR LOCAL TYCO ELECTRONICS SALES OFFICE.
 - ALL DIMENSIONS ARE NOMINAL. FOR REFERENCE ONLY UNLESS OTHERWISE STATED.
 - ALL DIMENSIONS ARE COMMON TO THE MAIN BODY. VARIATIONS ARE IN THE OPERATING LEVERS.
 - OP: OPERATING POSITION
FP: FREE POSITION

TE SALES PART No.	TE PART NO	DESCRIPTION	CHARACTERISTICS						△
			Operating Force	Releasing Force min	Pre Travel max	Operating Position	Over Travel min	Movement Differential max	
SP6DTBOLE	1-1478601-1	Microswitch, Pin Plunger	160 ±30 g	35 g	0,6 mm	8,4 ±0,3 mm	0,5 mm	0,2 mm	△
SP6DTBNLE	1-1478601-2	Microswitch, Norm Lever	45 ±15 g	8 g	3,0 mm	9,4 ±1,0 mm	1,0 mm	1,0 mm	△
SP6DTBLLE	1-1478601-3	Microswitch, Long Lever	25 ±10 g	5 g	3,7 mm	10,0 ±1,5 mm	1,5 mm	1,5 mm	△
SP6DTBNRE	1-1478601-4	Microswitch, Norm Roller	40 ±15 g	8 g	2,5 mm	15,0 ±0,8 mm	1,0 mm	1,0 mm	△
SP6DTBSME	1-1478601-5	Microswitch, Simu Roller	45 ±15 g	10 g	2,6 mm	10,8 ±0,8 mm	1,0 mm	1,0 mm	△

7	CONTACT	Ag ALLOY	
6	TERMINAL	BRASS SILVER PLATED	
5	TERMINAL	BRASS SILVER PLATED	
4	TERMINAL	BRASS SILVER PLATED	
3	BUTTON	PBT RESIN	BLACK
2	COVER	PBT RESIN	GREY
1	BASE	PBT RESIN	GREY
PART NO:	PART NAME:	MATERIAL/SURFACE:	OPTIONAL DESCRIPTION

PART LIST				DIMENSIONS: mm	
test dimen / Prüfmaß				auxiliary dimen / Hilfsmaß ()	
theor. dimen / theor. Maß				production control dimen / Fertigungskontrollmaß ()	
DIMEN. FOR MEASURE. TECHNOLOGY / MESSTECHN. REF. MAß []					
DEPARTMENT	DISE / R/SF				
DRAWER	27-03-08SA008712				
CHECKED	APPROVED				
T	21-04-09	VEIH	TOLERANCES SPECIFIED	APPROVED	
ECR-NO:	DATE	NAME	INFO	DATE	NAME

TOLERANCES UNLESS OTHERWISE SPECIFIED
 x +/-0,5mm
 .xx +/-0,2mm
 .xxx +/-0,1mm

SCALE:	NAME:	DATE:	NO:	REV. NO.:	NAME:
MICRO SWITCH 6A 160g RANGE		PCB TERMINAL		△ 1478601	
REPLACEMENT FOR:		REV. NO.:	DATE:	REV. NO.:	DATE:

THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TYCO ELECTRONICS AUSTRIA GMBH AND ITS AFFILIATES. IT MAY NOT BE DISCLOSED TO ANYONE OTHER THAN TYCO ELECTRONICS PERSONNEL WITHOUT WRITTEN AUTHORIZATION FROM TYCO ELECTRONICS AUSTRIA.