




1735482-1 Product Details

[Share](#) | [Print](#) | [Email](#)


1735482-1

0.8mm Free Height

Always EU RoHS/ELV Compliant (Statement of Compliance)

Product Highlights:

- Connector Style = Receptacle
- 40 Positions
- PCB Mounting Orientation = Vertical
- Board-to-Board Stack Height = 17.00 mm, 18.00 mm, 19.00 mm, 20.00 mm
- Gold (8) Contact Plating, Mating Area, Material

[View all Features](#)

TE Internal Number: 1735482-1

Active

[View 3D PDF](#)

[Add to My Part List](#) [Request Sample](#) [Find Similar Products](#) [Buy Product](#)

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [View Mating Products \(15\)](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

Documentation & Additional Information

Product Drawings:

- [RECEPTACLE 17MM HEIGHT FH 0.8MM B-T-B CONNECTOR WITH...](#) (PDF, English)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- [Free Height 0.8 mm Pitch Board-to-Board Connector \(SMT\)](#) (PDF, English)

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files: (CAD Format & Compression Information)

- [2D Drawing \(DXF, Version A\)](#)
- [3D Model \(IGES, Version A\)](#)
- [3D Model \(STEP, Version A\)](#)

Additional Product Images:

- [Product Photo](#)

Related Products:

- [Tooling](#)
- [Mating Products \(15\)](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- PCB Mounting Orientation = Vertical
- Family Name = Free Height
- Keyed = Yes
- Sealant = Without
- Cover Material = Steel

Termination Features:

- Solder Tail Contact Plating = Tin over Nickel

Dimensions:

- Board-to-Board Stack Height (mm [in]) = 17.00 [0.669], 18.00 [0.709], 19.00 [0.748], 20.00 [0.787]
- Height = 17H

Body Features:

- Locating Post(s) = With
- Vacuum Cover = With
- Locating Post Length = 0.5 mm

Contact Features:

- [Contact Plating, Mating Area, Material](#) = Gold (8)
- Contact Base Material = Copper Alloy

Housing Features:

- Connector Style = Receptacle
- Housing Color = Natural
- Housing Material = Liquid Crystal Polymer (LCP)
- UL Flammability Rating = UL 94V-0
- Housing Material Temperature = High

Configuration Features:

- [Number of Positions](#) = 40
- [Number of Rows](#) = Dual

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Reflow solder capable to 245°C, Reflow solder capable to 260°C
- [RoHS/ELV Compliance History](#) = Always was RoHS compliant

Packaging Features:

- [Packaging Method](#) = Tape & Reel

Other:

- Brand = AMP

Corporate Information

- [About TE](#)
- [Investors](#)
- [News Room](#)
- [Supplier Portal](#)
- [Careers](#)
- [Terms & Conditions](#)
- [Privacy Policy](#)

Quick Links

- [Check Distributor Inventory](#)
- [Cross Reference Products](#)
- [Find Documents & Drawings](#)
- [Product Compliance Support Center](#)
- [Site Map](#)

Customer Support

- [Email or Chat With Us](#)
- [Find a Phone Number](#)
- [Search Knowledge Base](#)
- [Manage Your Account](#)

Keep Me Informed

Receive TE News, Events & Technology Updates

