

**Product Details for 206612 -2**



**206612 -2**

[Active](#)

**CPC Connectors**

[RoHS Compliant](#) (Statement of Compliance)

**Product Highlights:**

- ? Connector
- ? Number of Positions = 22
- ? Plug
- ? Used With Socket Contacts
- ? Not Preloaded

[View all Features](#)

**Quick Links**

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [View Mating Products \(3\)](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

**Documentation & Additional Information**

**Product Drawings:**

- ? [PLUG ASSEMBLY, SHELL SIZE 23, STANDARD SEX, SERIES4, CP](#) (PDF, English)

**Catalog Pages/Data Sheets:**

- ? [CIRCULAR CONNECTORS FOR COMMERCIAL SIGNAL AND POWER ...](#) (PDF, English)

**Product Specifications:**

- ? None Available

**Application Specifications:**

- ? None Available

**Instruction Sheets:**

- ? None Available

**CAD Files:** ([CAD Format & Compression Information](#))

- ? [3D Model](#) (STEP, Version F)
- ? [3D Model](#) (IGES, Version F)
- ? [2D Drawing](#) (DXF, Version F)

[List all Documents](#)

**Additional Information:**

- ? [Product Line Information](#)

**Additional Product Images:**

- ? [Contact Arrangement](#)

**Related Products:**

- ? [Tooling](#)
- ? [Mating Products \(3\)](#)

**Product Features** (Please use the Product Drawing for all design activity)

**Product Type Features:**

- ? [Product Type](#) = Connector
- ? [Number of Positions](#) = 22
- ? [Gender](#) = Plug
- ? [Shell Size](#) = 23
- ? [Shell Type](#) = All Plastic
- ? [Product Series](#) = Series 4
- ? [Sealed](#) = No
- ? Number of Circuits = 2 (Power)/20 (MultiMate)

**Mechanical Attachment:**

- ? [Preloaded](#) = No
- ? [VDE Tested](#) = No

**Termination Related Features:**

- ? [Shell Thread Size](#) = 1 -3/8 - 18 UNEF -2A

**Body Related Features:**

- ? Used With = Socket Contacts
- ? [Mount Style](#) = Free Hanging
- ? Insulation Diameter (Signal Conductor) (mm [in]) = 3.81 [0.150]
- ? Insulation Diameter (Power Conductor) (mm [in]) = 5.59 [0.220]
- ? Coupling Ring Material = Polyphenylene

**Contact Related Features:**

- ? [Standard or Reverse Gender](#) = Standard

**Housing Related Features:**

- ? Housing Material = Thermoplastic
- ? Housing Color = Black
- ? Housing Flammability Rating = UL 94V -0

**Configuration Related Features:**

- ? [Reverse Numbering](#) = Without

**Industry Standards:**

- ? [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- ? [Lead Free Solder Processes](#) = Not relevant for lead free process
- ? RoHS/ELV Compliance History = Always was RoHS compliant

**Conditions for Usage:**

- ? [Terminate To](#) = Wire

**Other:**

- ? Brand = AMP