ThumbPointer™ (Stick Controller)

Compact size, standard type. Also available with lever return mechanism





■ Typical Specifications (Potentiometer)

| Items | RKJXK | RKJXV | |
|---------------------------|---|-------------------------------|--|
| Rated power | 0.0125W | | |
| Maximum operating voltage | 50V AC, 5V DC | | |
| Operating angle | 60° ±6° | 23° max. in each direction ** | |
| Operating force | 8mN·m max. (Not lever return type) 6±4mN·m (Lever return type) | 14±10mN·m | |
| Operating life | 100,000 cycles | 2,000,000 cycles | |

Note

If the lever is tilted more than 23° from the vertical position, operating feel irregularities or return mechanism errors may occur. Therefore, please do not tilt more than 23°.

■ Typical Specifications (Center-push)

| Items | RKJXK | RKJXV | |
|-----------------|--|--|--|
| Ratings (max.) | 50mA 12V DC | | |
| Operating force | 5.2±2.6N | 7.4±3N | |
| Travel | 0.5 ^{+0.5} _{-0.4} mm | 0.4 ^{+0.5} _{-0.3} mm | |
| Operating life | 100,000 cycles | 500,000 cycles | |

Product Line

| Product No. | Lever return | Center-push | Total resistance (kΩ) | Resistance | Minimum ord | Drawing | |
|--------------|--------------|---------------|-----------------------|------------|-------------|---------|-----|
| T TOUGET NO. | mechanism | Ceriter-pusir | | taper | Japan | Export | No. |
| RKJXK122400Y | With | With | | B(OB) | 500 | 1,000 | 1 |
| RKJXK122000D | VVICII | Without | 10 | | | | 2 |
| RKJXK1210002 | Without | Without | | | | | |
| RKJXV1224005 | With | With | | | 1,420 | 1,420 | 3 |
| RKJXV1220001 | VVILII | Without | | | 1,420 | | 4 |

Packing Specifications


Tray

| Product No. | Number of pa | Export package measurements (mm) | | |
|--------------------|--|----------------------------------|-------------|--|
| Froduct No. | 1 case / Japan 1 case / export packing | | | |
| RKJXK | 500 | 1,000 | 540×373×225 | |
| RKJXV 1,420 | | 1,420 | 544×364×178 | |



Dimensions Unit:mm PC board mounting hole dimensions (Viewed from mounting side) Photo No. Style RKJXK1224 6-01 hole 1 Return position 4-1.35 X1 Square hole Prohibited wiring area RKJXK1210 RKJXK1220 VR1 All directions 2 Return position Prohibited wiring area RKJXV1224 Lever return position 3 Height of boss Prohibited wiring area

■ Dimensions



| Type | | | Potentiometer type | | | | | |
|---------------------------|-----------------------------|---------------------------|---|----------------------------------|---|-----------------------------------|--|--|
| Series | | | RKJXK | RKJXV | RKJXY | RKJXU | | |
| Photo | | | | | | | | |
| Dimensions | W | | 20.7 | 17.8 | 19.6 | 18.6 | | |
| (typical valu | | | 25.4 | 21.3 | 18.1 | 24.3 | | |
| (mm) | | Н | 12.9 | 11.2 | 4.9 | 5.2 | | |
| Number of | foperating | shafts | | Single | e-shaft | | | |
| Shaf | t mater | ial | Metal | | Resin | | | |
| | nal reso | | | Conti | nuous | | | |
| Directional (tact | operating tile feeling | | Without | | | | | |
| Lever ret | urn mech | nanism | With / Without | t With | | | | |
| Center- | push s | witch | With / Without Without | | | | | |
| Е | ncoder | | Without | | | | | |
| Operating : | temperatur | e range | −10°C to +70°C | | | | | |
| Operating | Directional operation | | 100,000 cycles | 2,000,000 cycles | 1,000,000 cycles | 2,000,000 cycles | | |
| life | Center-push | | 100,000 cycles | 500,000 cycles | _ | _ | | |
| Autor | Automotive use | | _ | _ | _ | _ | | |
| Life cycle (availability) | | ability) | * 2 | ★ 2 | | * 2 | | |
| | Insulation resistance | | 100MΩ min. 250V DC — | | _ | | | |
| Electrical performance | Voltage proof | | 250V AC for 1 minute | | | | | |
| , | Slider | noise | 300mV p-p max. by JIS method | | | | | |
| | Directional operating force | | 8mN·m max. Without Lever return mechanism 6±4mN·m With Lever return mechanism | 14±10mN·m | With knob type 0.43±0.25N (3.33±2.0mN·m) Without knob type 3.33±2.0mN·m | 0.75±0.3N | | |
| Mechanical | Push operating force | | 5.2±2.6N | 7.4±3N | _ | _ | | |
| performance | Lever return precision | | ±5° | | | ±0.1mm | | |
| | Actuator | Push / pull directions | 50N min. (Push/Pull) | 98N min. (Push), 50N min. (Pull) | 100N min. (Push), 49N min. (Pull) | 100N min. (Push), 30N min. (Pull) | | |
| | strength | Operating direction | 0.3N·m | _ | 50 | NC | | |
| | Cold | | -30℃ 96h | | | | | |
| Environmental performance | Dry heat | | 80°C 96h | | | | | |
| | Damp | heat | | 60°C, 90 to | 95%RH 96h | | | |
| | Page | | 42 | 428 431 | | | | |

Potentiometer Type / Soldering Conditions

Reference for Manual Soldering

| Series | Tip temperature | Soldering time | No. of solders | |
|--------------|-----------------|----------------|----------------|--|
| RKJXK, RKJXV | 350°C max. | 3s max. | 1 time | |

■ Reference for Dip Soldering

| Series | Preheating | | Dip soldering | | No. of solders |
|--------|-------------------------------|--------------|-----------------------|----------------|-----------------|
| Jenes | Soldering surface temperature | Heating time | Soldering temperature | Soldering time | INU. UI SUIUEIS |
| RKJXK | 90 to 100℃ | 45s max. | 255 to 260℃ | 2 to 3s | 1 time |
| RKJXV | 90 to 120℃ | 60s max. | 260℃ | 5s | 1 time |

Potentiometer Type / Cautions

(Circuit Used for Analog Stick Controller)

We recommend you use the potentiometer type in a voltage divider type as shown in Fig. A.

(Impedance on the Output Side)

Since this pot is designed to use with its output is connected directly to A/D port. Impedance is considered to be mega ohm level. Then contact resistance in the pot is higher. Please refer to Flg-1. So when you use it in the circuit like Flg-2.Please make sure that impedance should be over than 1M-ohm.





Fig.A.Voltage divider type

(Dew Condensation)

Avoid using the product when condensation or drops of water might occur inside the product. Otherwise, insulation deterioration or shorting may occur.

(Soldering)

Do not employ wiring designs and soldering methods as illustrated in the schematic drawing. Molten solder flowing over the upper surface of PC board can cause imperfect contacts. Solder all metal inserted fixing including terminals & metal lugs into a substrate.



(Stress Being Applied to the Terminals)

Always be careful not to apply excessive stress on the terminals. Design appropriate soldering conditions.

(Handling of Variable Resistors Equipped with Switches)

Exercise care when packing or storing. Packaging or storing while load is applied to the shaft may cause a malfunction in performance.

(Storage)

- ① Store the products as delivered, at a normal temperature and humidity, without direct sunshine and corrosive gas ambient. Use them at an earliest possible timing, not later than six months upon receipt.
- ② After breaking the seal, keep the products in a plastic bag to shut out ambient air, store them in the same environment as above, and use them up as soon as possible.
- 3 Do not stack too many switches.

The above operation notes are quoted from the

"Precaution and Guideline of Potentiometer for Electrical Devices", a technical report issued by the Japan Electronics and Information Technology Industries Association EIAJ RCR-2191A (in March 2002).

For details, refer to the original technical report.

