


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 20
 © COPYRIGHT 20 BY - ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS					
HM	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
		A		RLSD; ECO-13-007405	01MAY2013	GG	MS

110 BLOCK
JUMPER BOARD
ASSEMBLY



- 1. MATERIAL: PRINTED CIRCUIT BOARD - LAMINATED PLASTIC SHEET, 1.57[.062] THICK. 110 BLOCK - POLYMER MOLDING COMPOUND, IVORY. TERMINALS - PHOSPHOR BRONZE PLATED WITH 3.81um[.000150] MINIMUM THICK TIN-LEAD OVER 1.27um[.000050] MINIMUM THICK NICKEL UNDERPLATE. MOUNTING TRACK - POLYMER MOLDING COMPOUND, BLACK.
- 2. 110 BLOCK WILL TERMINATE 22-26 AWG SOLID CONDUCTORS OR 22-26 AWG 7 STRAND CONDUCTORS.
- 3. ALL DIMENSIONS ARE NOMINAL UNLESS OTHERWISE SPECIFIED.
- 4. PACKAGE 5 KITS PER CARTON.
- 5. PRODUCTS PERFORMANCE MEETS OR EXCEEDS THE REQUIREMENTS OF TIA 568, LATEST ISSUE.

9.78
[.385]

26.31
[1.036]

13.51
[.532]

15.88
[.625]

106.9
[4.21]

126.5±1
[4.98±.04]

Ø4.19-4.44
[.165-.175]
2 PLACES

MOUNTING TRACK
ASSEMBLY

2111682-1
PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN G. GARRETT 01MAY2013	TE Connectivity	
DIMENSIONS: MM [INCHES]		CHK M. SHORE 01MAY2013		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD M. SHORE 01MAY2013	NAME JUMPER BOARD KIT, 110 BLOCK UNIVERSAL CATEGORY, CAT 5E AND CAT 6	
0 PLC ±	±	PRODUCT SPEC	SIZE CAGE CODE DRAWING NO RESTRICTED TO	
1 PLC ±	±	APPLICATION SPEC	A200779 C-2111682	
2 PLC ±	±	WEIGHT	SCALE 2:1 SHEET 1 OF 1 REV A	
3 PLC ±	±	Customer Drawing		
4 PLC ±	±			
ANGLES ±	±			
FINISH				