


2-603326-7 Product Details



2-603326-7

TE Part Number: 2-603326-7

 [Active](#)

 [Add to Part List](#)

Heat Shrink Tubing

 [Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

Product Highlights:

- Jacket Tubing
- Military Application
- Operating Temperature = -55 - 135 °C
- Inside Diameter (Min-Max) = 3.18 - 6.35 mm
- Without Sealant

[View all Features](#) | [Find Similar Products](#)

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

Documentation & Additional Information

Product Drawings:

- [AMPSULATION VPF21 AND FP21](#), (PDF, English)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- [Heat Shrink Tubing](#) (PDF, English)

Instruction Sheets:

- None Available

CAD Files:

- None Available

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- [Product Type](#) = Jacket Tubing
- [Sealant](#) = Without
- Style = FP21
- Size = 6.35 [1/4]
- Color = Black
- Material = Polyolefin
- Proprietary Name = AMPSULATION

Body Related Features:

- [Marked](#) = No
- [Shrink Ratio](#) = 2:1
- [Wall Style](#) = Thin
- [Wall Thickness - Full Recovery \(Nominal\) \(mm \[in\]\)](#) = 0.64 [0.025]
- [Length \(M \[ft\]\)](#) = 60.96 [200.00]

Contact Related Features:

- Approved Standards = MIL I 23053

Housing Related Features:

- [Inside Diameter \(Min-Max\) \(mm \[in\]\)](#) = 3.18 - 6.35 [0.125 - 0.250]

Industry Standards:

- Government/Industry Qualification = Yes
- Government/Industry Part Number = M23053/5-106-0
- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process
- RoHS/ELV Compliance History = Always was RoHS compliant

Conditions for Usage:

- Operating Temperature (°C) = -55 - +135

Operation/Application:

- Application = Military

Packaging Related Features:

- Packaging Method = Reel
- Weight per Linear Foot (g [lb]) = 2.54 [0.0056]

Other:

- Brand = AMP