



PIDG Terminals

PIDG Ring Tongue Terminals

Material and Finish
Insulation — Nylon
Terminal Body and Metallic Sleeve — Copper per ASTM B-152, (in plated per MIL-T-10727)

Wire Size Circular Mills [mm ²]	Tongue Material Thickness Max.	Stud Size	Dim. W	Terminal Insulation Color	Wire Insulation Diameter Max.	Part Numbers Loose Piece
26-22 202-810 [0.10-0.41]	0.51 .020	2	3.56	Yellow	2.08	323912*
		M2	.140			
		4	5.16	Yellow	2.08	323914*
		M3.5	.203			
		6	5.16	Yellow	2.08	323915*
		M3.5	.203			
8	6.35	Yellow	2.08	323916*		
M4	.250					
10	6.35	Yellow	2.08	324075*		
22-16 509-3,260 [0.26-1.65]	0.84 .033	2	5.54	Red	3.18	328657*
		M2	.218			
		4	5.54	Red	3.56	31880*
		M3.5	.281			
		6	7.14	Red	3.56	36152*
		M3.5	.281			
		8	7.92	Red	3.56	31890*
		M4	.312			
		10	7.92	Red	3.56	36154*
		1/4	11.91	Red	3.56	31894*
M6	.469					
5/16	11.91	Red	3.56	31895*		
M8	.469					
3/8	13.49	Red	3.56	31897*		
16-14 2,050-5,180 [1.04-2.62]	0.84 .033	4	6.35	Blue	4.32	328996*
		M3.5	.250			
		6	6.35	Blue	4.32	320619*
		M3.5	.250			
		8	6.71	Blue	4.32	320565*
		M4	.343			
		10	8.71	Blue	4.32	36160*
		1/4	11.91	Blue	4.32	321045*
M6	.469					
5/16	11.91	Blue	4.32	328998*		
M8	.469					
3/8	13.49	Blue	4.32	328999*		
16-14D [†] 2,050-5,180 [1.04-2.62]	1.27 .050	8	6.71	Yellow/Blk.	5.84	320627*
		M4	.343			
		10	8.71	Yellow/Blk.	5.84	320630*



*Available in small packaging quantities.
[†]Heavy duty for extra mechanical strength.