


5 Gang Access Floor Workstation Module

PART NUMBER 557601-X




X denotes color: -1 = Almond, -2 = Storm Gray, -3 = Black, -4 = NEMA Gray

Product Facts

- :: Five Gang – any combination of power and communications
- :: Accepts all standard AFWM Faceplates (see page 94)
- :: Outlets flip up above floor for easy access
- :: Large cable opening enables disassembly and relocation without re-termination of communications connectors
- :: Suitable for use in non-environmental air spaces
- :: Dimensions: 8" x 12", 5.5" min. floor height (top of raised floor to top of main floor surface)

4 Gang Access Floor Workstation Module

PART NUMBER 406376-X




X denotes color: -1 = Almond, -2 = Storm Gray, -3 = Black, -4 = NEMA Gray

Product Facts

- :: Four Gang – two accept duplex power receptacles, Two accept standard FLEX-MODE Electrical Faceplates
- :: Shallow profile provides easy access to connections
- :: Complies with NEC 300-22(c) requirements for use in environmental air spaces
- :: Dimensions: 8" x 12", 2.6" min. floor height (top of raised floor to top of main floor surface)

3 Gang Access Floor Workstation Module

PART NUMBER 558716-X



X denotes color: -1 = Almond, -2 = Storm Gray, -3 = Black, -4 = NEMA Gray

Product Facts

- :: Three Gang – any combination of power and communications
- :: Accepts all standard AFWM Faceplates (see page 94)
- :: Complies with NEC 300-22(c) requirements for use in environmental air spaces
- :: Dimensions: 7.375" x 7.375", 5.5" min. floor height (top of raised floor to top of main floor surface)

3.3

OUTLETS, FACEPLATES AND ACCESSORIES

92