


## 1717831-1 Product Details

[Live Product Chat](#)



### 1717831-1

TE Part Number: 1717831-1

[Active](#)

[Add to Part List](#)

### Memory Sockets

[Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

#### Product Highlights:

- Mini PCI
- Gold Flash Contact Mating Area Plating Material
- Number of Positions = 52
- Row-to-Row Spacing = 6.20 mm
- .80 mm Centerline

[View all Features](#) | [Find Similar Products](#)

### Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

### Documentation & Additional Information

#### Product Drawings:

- [SEMI HARD TRAY & EMBOSS TAPE SUPPLY MINI PCI EXPRESS...](#) (PDF, English)

#### Catalog Pages/Data Sheets:

- None Available

#### Product Specifications:

- [MINI PCI EXPRESS CONNECTOR](#) (PDF, Japanese)
- [MINI PCI EXPRESS H7.0](#) (PDF, Japanese)

#### Application Specifications:

- None Available

#### Instruction Sheets:

- None Available

#### CAD Files: ([CAD Format & Compression Information](#))

- [2D Drawing](#) (DXF, Version C)
- [3D Model](#) (IGES, Version C)
- [3D Model](#) (STEP, Version C)

[List all Documents](#)

#### Additional Information:

- [Product Line Information](#)

#### Related Products:

- [Tooling](#)

### Product Features (Please use the Product Drawing for all design activity)

#### Product Type Features:

- Product Type = Mini PCI
- [Number of Positions](#) = 52
- [Module Orientation](#) = Right Angle
- Comment = Order Latch 1717832-1 separately.

#### Body Related Features:

- [Row-to-Row Spacing \(mm \[in\]\)](#) = 6.20 [0.244]
- [Centerline \(mm \[in\]\)](#) = 0.80 [0.031]
- [Number of Rows](#) = Dual
- Ejector Type = Locking
- [Ejector Location](#) = Both Ends
- Boss = With

#### Contact Related Features:

- Contact Mating Area Plating Material = Gold Flash
- [Contact Mount](#) = Surface Mount
- Contact Material = Copper Alloy

#### Housing Related Features:

- Housing Material = High Temperature Thermoplastic

#### Configuration Related Features:

- [Stack Height \(mm \[in\]\)](#) = 4.00 [0.157]
- [Insertion Style](#) = Cam-In

#### Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Reflow solder capable to 245°C
- RoHS/ELV Compliance History = Always was RoHS compliant

#### Packaging Related Features:

- Packaging Method = Tray
- Packaging Quantity = 70

#### Other:

- Brand = AMP