


**Product Details for 2 -5178238 -4**



**1.27 [.050] Series II and Series III Connectors**

[RoHS Compliant \(Statement of Compliance\)](#)

**Product Highlights:**

- ? Mating Type = Receptacle
- ? Number of Positions = 26
- ? Terminate To Printed Circuit Board
- ? Right Angle Mount Angle
- ? With Special PCB Retention

[View all Features](#)

**2 -5178238 -4**

[Active](#)

**Quick Links**

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

**Documentation & Additional Information**

**Product Drawings:**

- ? [RECEPTACLE HDR ASSY \(3.1mm\) RETENTION LEG TYPE STAND...](#) (PDF, English)

**Catalog Pages/Data Sheets:**

- ? None Available

**Product Specifications:**

- ? [CHAMP.050 Series\(II\) Connector Wire to Board Type](#) (PDF, English)

**Application Specifications:**

- ? None Available

**Instruction Sheets:**

- ? None Available

**CAD Files:** ([CAD Format & Compression Information](#))

- ? [3D Model](#) (STEP, Version A)
- ? [3D Model](#) (IGES, Version A)
- ? [2D Drawing](#) (DXF, Version A)

[List all Documents](#)

**Additional Information:**

- ? [Product Line Information](#)

**Related Products:**

- ? [Tooling](#)

**Product Features** (Please use the Product Drawing for all design activity)

**Product Type Features:**

- ? [Mating Type](#) = Receptacle
- ? [Number of Positions](#) = 26
- ? [Mount Angle](#) = Right Angle
- ? [Special PCB Retention](#) = With
- ? [Mating Connector Lock](#) = Without
- ? [Product Series](#) = Series II
- ? PCB Thickness (mm [in]) = 1.57 – 2.36 [0.062 – 0.093]
- ? Special PCB Retention Method = Boardlock
- ? Panel Thickness (mm [in]) = 2.01 [0.079]
- ? Color = Black
- ? Frame Material = Die Cast Zinc
- ? Shield Material = Steel
- ? Comment = Alternate tail lengths 3.90 [.153] and 2.20 [.087] available

**Mechanical Attachment:**

- ? [Panel Attachment](#) = With
- ? Boardlock Material = Phosphor Bronze
- ? Boardlock Plating = Tin over Nickel

**Termination Related Features:**

- ? Termination Post Length (mm [in]) = 3.10 [0.122]
- ? Solder Tail Plating = Tin

**Body Related Features:**

- ? Centerline (mm [in]) = 1.27 [0.050]
- ? Frame Plating = Nickel
- ? Shield Plating = Nickel over Copper

**Contact Related Features:**

- ? [Contact Mating Area Plating](#) = Gold (30)
- ? Contact Material = Phosphor Bronze

**Housing Related Features:**

- ? [Housing Material Temperature](#) = Standard
- ? Housing Material = Glass - Filled Nylon
- ? Housing Flammability Rating = UL 94V -0

**Industry Standards:**

- ? [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- ? [Lead Free Solder Processes](#) = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C
- ? RoHS/ELV Compliance History = Always was RoHS compliant

**Conditions for Usage:**

- ? [Terminate To](#) = Printed Circuit Board

**Other:**

- ? Brand = AMP