



Search bar: What can we help you find?

150730 Product Details

Share | Print | Email



150730

TE Internal Number: 150730

Active

View 3D PDF

Miscellaneous Terminals

Always EU RoHS/ELV Compliant (Statement of Compliance)

Product Highlights:

- Insulation Support
- Wire Range = 0.30-1.40² [22-16] mm [AWG]
- Not For Use With Double Wire
- Length = 28.50 mm
- Color = Red

[View all Features](#)

Quick Links

- ▶ Pricing & Availability
- ▶ Search for Tooling
- ▶ Product Feature Selector
- ▶ Contact Us About This Product

[Add to My Part List](#) | [Request Sample](#) | [Find Similar Products](#) | [Buy Product](#)

Documentation & Additional Information

<p>Product Drawings:</p> <ul style="list-style-type: none"> • TERMINAL, TAB, PIDG, WIRE SIZE 22-16 (PDF, English) <p>Catalog Pages/Data Sheets:</p> <ul style="list-style-type: none"> • None Available <p>Product Specifications:</p> <ul style="list-style-type: none"> • None Available <p>Application Specifications:</p> <ul style="list-style-type: none"> • None Available <p>Instruction Sheets:</p> <ul style="list-style-type: none"> • None Available <p>CAD Files: (CAD Format & Compression Information)</p> <ul style="list-style-type: none"> • 2D Drawing (DXF, Version A) • 3D Model (IGES, Version A) • 3D Model (STEP, Version A) 	<p>Related Products:</p> <ul style="list-style-type: none"> • Tooling
--	---

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

<p>Product Type Features:</p> <ul style="list-style-type: none"> • Insulation Support = Insulation Support • Color = Red • Finish = Tin • Bulb = Without • Insulation = Yes • Wire/Cable Type = Regular Wire <p>Dimensions:</p> <ul style="list-style-type: none"> • Length (mm [in]) = 28.50 [1.122] • Insulation Diameter (mm [in]) = 2.03-3.18 [.080-.125] <p>Body Features:</p> <ul style="list-style-type: none"> • Wire Range (mm [AWG]) = 0.30-1.40² [22-16] • Double Wire = No • Material = Copper • Body Style = Straight • Insulation Sleeve Material = Nylon 	<p>Configuration Features:</p> <ul style="list-style-type: none"> • Diode = Without <p>Industry Standards:</p> <ul style="list-style-type: none"> • RoHS/ELV Compliance = RoHS compliant, ELV compliant • Lead Free Solder Processes = Not relevant for lead free process • RoHS/ELV Compliance History = Always was RoHS compliant <p>Packaging Features:</p> <ul style="list-style-type: none"> • Packaging Method = Loose Piece <p>Other:</p> <ul style="list-style-type: none"> • Brand = AMP • Proprietary Name = PIDG
--	--

Corporate Information

- [About TE](#)
- [Investors](#)
- [News Room](#)
- [Supplier Portal](#)
- [Careers](#)
- [Terms & Conditions](#)
- [Privacy Policy](#)

Quick Links

- [Distributor Inventory](#)
- [Product Cross Reference](#)
- [Documents & Drawings](#)
- [Product Compliance Support Center](#)
- [Site Map](#)

Customer Support

- [Email or Chat With Us](#)
- [Find a Phone Number](#)
- [Knowledge Base](#)
- [Manage Your Account](#)

Keep Me Informed

Receive TE News, Events & Technology Updates

Enter your email address

