




[CONNECTORS](#)

[RF CONNECTORS](#)



✓ Active

TE CONNECTIVITY (TE)

SHV JACK

Standard Coax | SH6

225087-5

TE Internal Number: 225087-5

Not EU RoHS Compliant

Not EU ELV Compliant

Connector Interface SHV

Connector Style Jack

Cable Type Belden 9209, Belden 9269, Belden 9291, RG 124, RG 140, RG 210, RG 59, RG 59A, RG 59B, RG 62, RG 62A, RG 62B

Connector & Contact Terminates To Wire & Cable

Termination Method to Wire & Cable Crimp

[↓ PRODUCT DRAWING](#)
English

[↓ 3D PDF](#)

DOCUMENTATION

Product Drawings

JACK, STANDARD HIGH VOLTAGE

PDF (TIFF AVAILABLE)

English

CAD Files

Customer View Model

2D_DXF.ZIP

English

Customer View Model

3D_IGS.ZIP

English

Customer View Model

3D_STP.ZIP

English

3D PDF

PDF

English

Product Specifications

Application Specification

Coaxial High Voltage Connectors

TIF

English

Coaxial High Voltage Connectors

PDF

English

Product Specification

COAXICON Standard High Voltage Connector

PDF

English

Instruction Sheets

Instruction Sheet (U.S.)

AMP STANDARD HIGH VOLTAGE (SHV) COAXICON JACK AND BULKHEAD JACK CONN

PDF

English

AMP STANDARD HIGH VOLTAGE (SHV) COAXICON JACK AND BULKHEAD JACK CONN

TIF

English

FEATURES



Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

Connector Interface SHV

Connector Style Jack

Connector & Contact Terminates To Wire & Cable

Body Features

Body Plating Material Nickel

Contact Features

Crimp Type Dual

Center Contact Plating Material Gold

Termination Features

Termination Method to Wire & Cable Crimp

Usage Conditions

Cable Type Belden 9209, Belden 9269, Belden 9291, RG 124, RG 140, RG 210, RG 59, RG 59A, RG 59B, RG 62, RG 62A, RG 62B

Other

Dielectric Material PTFE

PRODUCT COMPLIANCE



Statement of Compliance

Statement of Compliance

PDF
