



THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
 © COPYRIGHT - By - ALL RIGHTS RESERVED.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL DRAWING	03FEB2015	GSK	BvH
	A1	ECR-17-001194	31JAN2017	RK	PFR



VIEW A

NOTES:

- 1 PACKAGING: ACC. TO TE SPEC. 107-18032
- 2 ELECTRICAL TEST ACCORDING TE SPECIFICATION 108-18857.
SHORT-CIRCUIT AND CONTINUITY TEST AT 500V DC, 0.1s
- 3 WIRING SCHEMA ACC. TO TIA/EIA-568-B AS SHOWN IN WIRING SCHEDULE

WIRING SCHEDULE 3

CAVITY SIDE A	COLOR	CAVITY SIDE B
1	WH/OG	1
2	OG	2
3	WH/GN	3
4	BU	4
5	WH/BU	5
6	GN	6
7	WH/BN	7
8	BN	8

10	HiFlex MultiPurpose 70°C PUR	2-2205129-6
5	HiFlex MultiPurpose 70°C PUR	2-2205129-5
3	HiFlex MultiPurpose 70°C PUR	2-2205129-4
2	HiFlex MultiPurpose 70°C PUR	2-2205129-3
1	HiFlex MultiPurpose 70°C PUR	2-2205129-2
0.5	HiFlex MultiPurpose 70°C PUR	2-2205129-1
10	HI 125°C TPE	1-2205129-6
5	HI 125°C TPE	1-2205129-5
3	HI 125°C TPE	1-2205129-4
2	HI 125°C TPE	1-2205129-3
1	HI 125°C TPE	1-2205129-2
0.5	HI 125°C TPE	1-2205129-1
10	STD 110°C PVC	-2205129-6
5	STD 110°C PVC	-2205129-5
3	STD 110°C PVC	-2205129-4
2	STD 110°C PVC	-2205129-3
1	STD 110°C PVC	-2205129-2
0.5	STD 110°C PVC	-2205129-1
Length/m	Cable version	TE PN

OBSOLETE

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 03FEB2015 SATHISH KUMAR .G	TE Connectivity		
DIMENSIONS: mm		CHK 03FEB2015 B.VELDHOVEN			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD 03FEB2015 A.VAN ZANDVOORT	NAME CA MINI IO TYPE I PIGTAIL		
0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± 1°		PRODUCT SPEC 108-78955	-		
MATERIAL		APPLICATION SPEC 114-5506	SIZE A3	CAGE CODE 00779	DRAWING NO C-2205129
FINISH		WEIGHT	RESTRICTED TO		
CUSTOMER DRAWING			SCALE NTS	SHEET 1 OF 1	REV A1