


Electronics
[English](#) [日本語](#)
a vital part of your world
**Find
Answers:**

Monday, 10 October, 2005

CATALOG

 → [Cross Reference](#)
[Competitive Products](#)
[Military Spec P/Ns](#)
[Tyco Brand P/Ns](#)

 → [Part Number Search](#)

 → [Document Search](#)

 → [Product Type Search](#)

 → [Product Family Search](#)

 → [Alphabetical Search](#)

 → [RoHS/ELV Compliance & Alternates](#)

 → [CAD Model Search](#)

 → [Brand Search](#)

 → [Tool Search](#)

 → [Multiple Part Comparison](#)

 → [Lead Free Solutions](#)

 → [Help/Glossary](#)
[Home](#)

 e-bulletin newsletter
SUBSCRIBE NOW!
 click here

Fiber Optic Products
↳ Fiber Optic Cable Assemblies
AMP **504970-5**  [Active](#)
[Not ELV or RoHS Compliant](#)
(Corporate P/N: 504970-5)
[Search for Compliant \(RoHS/ELV\)](#)
[Alternates](#)
[Search for Parts](#)

Document links for this part cannot be displayed. Your browser does not support inline frames or is currently configured not to display inline frames. Inline frames are supported in both Internet Explorer 5 and Netscape 6, as well as all later versions of these browsers.

Related Part Information

General Information	eCommerce	Related Part Information
<ul style="list-style-type: none"> ✦ General Info ✦ Sales Info ✦ Assembly Subcontractors 	<ul style="list-style-type: none"> ✦ Pricing ✦ Product Availability 	<ul style="list-style-type: none"> ✦ Tooling

Photos & Line Drawings - The photographs and/or line drawings are representative images of a product for viewing purposes only.

[Product Photo](#)
Searchable Features:

Brand:	AMP
RoHS/ELV Compliance:	Not ELV/RoHS compliant
Lead Free Solder Processes:	Not relevant for lead free process
Product Type:	Cable Assembly
Cable Assembly Type:	SC to SC
Fiber Type:	62.5/125
Mode:	Multimode
Cable Type:	Simplex
Cable Diameter (mm [in]):	3.00 [.118]

Other Properties:

AMP Logo:	With
Insertion Loss (dB):	0.52

Number of Fibers:	1
Flammability Rating:	Riser (UL OFNR/ CSA FT-4)
Cable Buffering:	Tight
Cable Color:	Orange
Length (M [ft]):	10.00 [32.808]
Mode Conditioned Launch Cable Assembly:	No
Connector(s) Exit Angle to Connector(s) Exit Angle:	180° to 180°
Boot Body Style - Left:	Long
Boot Color - Left:	Beige
Boot Body Style - Right:	Long
Boot Color - Right:	Beige
Ferrule Material:	Ceramic
Fibre Channel:	No

[Copyright and Privacy Statement](#)
Visit [Tyco International Ltd.](#)

[[Products](#) | [Catalog](#) | [Brands](#) | [Industries](#) | [Commerce](#) | [Supplier](#) | [Contact Us](#) | [About](#) | [Home](#)]