

2 - 696200 - 2 Product Details

Live Product Chat US Only
8:30am - 5pm ET, Mon - Fri



2 - 696200 - 2

[Active](#)

Miscellaneous Terminals

[Always EU RoHS/ELV Compliant](#) ([Statement of Compliance](#))

Product Highlights:

- ? Wire Pin
- ? Insulation Support
- ? Wire Range = 3.00 - 6.00 ² [12 - 10] mm [AWG]
- ? Not For Use With Double Wire
- ? Length = 28.50 mm

[View all Features](#) | [Find Similar Products](#)

Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

Documentation & Additional Information

Product Drawings:

- ? [TERMINAL, WIRE PIN, PIDG WIRE SIZE, 12 - 10 AWG](#) (PDF, English)

Catalog Pages/Data Sheets:

- ? None Available

Product Specifications:

- ? None Available

Application Specifications:

- ? None Available

Instruction Sheets:

- ? None Available

CAD Files:

- ? None Available

Related Products:

- ? [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- ? Product Type = Wire Pin
- ? [Insulation Support](#) = Insulation Support
- ? Color = Yellow
- ? Material = Copper
- ? Finish = Tin
- ? Shape = WIRE PIN -003
- ? Body Style = Straight
- ? Insulation = Yes
- ? Insulation Diameter (mm [in]) = 6.40 [.251] Max.
- ? Proprietary Name = PIDG
- ? Wire/Cable Type = Regular Wire

Body Related Features:

- ? [Wire Range \(mm \[AWG\]\)](#) = 3.00 - 6.00 ² [12 - 10]
- ? Double Wire = No
- ? Length (mm [in]) = 28.50 [1.122]
- ? Insulation Sleeve Material = Nylon
- ? DIN Wire Size (mm ²) = 2.50 - 6.00

Contact Related Features:

- ? Bulb = Without

Configuration Related Features:

- ? Diode = Without

Industry Standards:

- ? [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- ? [Lead Free Solder Processes](#) = Not relevant for lead free process
- ? RoHS/ELV Compliance History = Always was RoHS compliant

Packaging Related Features:

- ? Packaging Method = Tape Mounted

Other:

- ? Brand = AMP