


0358 Product Details

[Share](#) | [Print](#) | [Email](#)


0358

(1-1437397-2)

TE Internal Number: 1-1437397-2

Active

NEMA Terminal Blocks

[Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

Product Highlights:

- 300 Series Block Series
- NEMA Product Line
- Block Type = Fuse
- Contact Configuration = Strap Clamp
- In-Line Circuit Protection Application

[View all Features](#)

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

[Add to My Part List](#) [Request Sample](#) [Find Similar Products](#) [Buy Product](#)

Documentation & Additional Information

Product Drawings:

- None Available

Catalog Pages/Data Sheets:

- [BUCHANAN TERMINAL BLOCKS CATALOG - NEMA TERMINAL BLOCKS](#) (PDF, English)

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Additional Information:

- [Product Line Information](#)

Additional Product Images:

- [Line Drawing](#)
- [Typical Mounting Configuration](#)

Related Products:

- [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- Product Line = NEMA
- Screw Size = 8-32 Pan Head W/Clamp

Electrical Characteristics:

- Voltage Rating (VAC) = 600
- Amperes (A) = 25.0

Body Features:

- [Block Series](#) = 300 Series
- [Block Type](#) = Fuse
- Mount Style = Channel Mount (Dovetail Base)
- [Wire Range \(Solid and Stranded\)\[MCM\] \(AWG\)](#) = 18-8
- [Blown Fuse Indicator](#) = Without
- [Blown Fuse Indicator Type](#) = None
- Wire Strip Length (mm [in]) = 12.70 [0.500]

Contact Features:

- Contact Configuration = Strap Clamp
- Pitch (mm [in]) = 19.05 [0.750]

Housing Features:

- [Housing Material](#) = Phenolic - GF
- UL Flammability Rating = UL 94V-1

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process
- RoHS/ELV Compliance History = Always was RoHS compliant

Conditions for Usage:

- Temperature, Max. (°C) = 150

Operation/Application:

- Application = In-Line Circuit Protection

Packaging Features:

- Terminals Per Foot = 16

Other:

- [Fuse Puller](#) = With
- Brand = Buchanan

Corporate Information

[Who We Are](#)
[Investors](#)
[News Room](#)
[Supplier Portal](#)
[Careers](#)

Quick Links

[Check Distributor Inventory](#)
[Cross Reference](#)
[Find Documents & Drawings](#)
[Product Compliance Support Center](#)
[Site Map](#)

Customer Support

[Email or Chat With Us](#)
[Find a Phone Number](#)
[Search Knowledge Base](#)
[Manage your Account](#)

Keep Me Informed

Receive TE News, Events & Technology Updates

